

REVISIONS



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	19MAR2015	DL	CW
	B	ECR-15-013292	24SEP2015	DL	CW
	C	ECR-21-105887	26JUL2021	BS	CW

NOTES:

- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 250 V
RATED CURRENT: 10 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 2.5 KV
POLLUTION DEGREE: 2
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
OPERATION TEMPERATURE: $-40-+125^{\circ}C$
WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)
CONTACT TYPE: ROLLED CRIMP CONTACT
- CONTACT NEED TO BE ORDERED SEPARATELY.






注释:

- 技术参数:
绝缘材料: PC
额定电压: 250V
额定电流: 10A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 2.5 KV
污染等级: 2
阻燃等级: UL94V-0
插拔次数: 500次
工作温度: $-40-+125^{\circ}C$
接线范围: 0.14-2.5 mm² (26-14 AWG)
接线类型: 卷皮式冷压接
- 端子需要单独订购.



M4 SCREW
RECOMMENDED TIGHTENING TORQUE 1.2Nm


4 X M3 SCREW
RECOMMENDED TIGHTENING TORQUE 0.5Nm



PANEL CUT OUT FOR INSERTS FOR USING
WITHOUT HOODS/HOUSINGS

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

FINISH

-

DWN 18MAR2015

DAVID LI

CHK 18MAR2015

CHRIS WANG

APVD 18MAR2015

XU XIANG

PRODUCT SPEC

108-137043

APPLICATION SPEC

114-137043

WEIGHT

-

CUSTOMER DRAWING

HDD-042-FJ

T2030423201-000

DESCRIPTION

PART NUMBER



TE Connectivity

NAME

HDD-042-FJ

SIZE

A3

CAGE CODE

-

DRAWING NO

©-T2030423201000

RESTRICTED TO

SCALE

1:1

SHEET

1 OF 1

REV

C