







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	01NOV2016	DW	CW
	B	ECR-21-106515	21JUL2021	SQ	CW



M4 SCREW,
RECOMMENDED
TIGHTENING
TORQUE 1.2Nm
M4螺丝, 推荐扭力矩为1.2Nm

4X M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3螺丝, 推荐扭力矩为0.5Nm



NOTES:


- I. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 500V
RATED CURRENT: 16A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.5mm²~2.5mm² (AWG20-AWG14)
CONTACT FINISH: SILVER PLATED
CONTACT TYPE: DOUBLE SPRING CLAMP

注释:

- I. 技术参数:
绝缘材料: PC
额定电压: 500V
额定电流: 16A
绝缘电阻: $\geq 400M\Omega$
脉冲电压: 6KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500 次
接线范围: 0.5mm²~2.5mm² (AWG20-AWG14)
端子表面处理: 镀银
接线类型: 双弹片连接

PANEL CUT OUT DIMENSION FOR INSERT
WITHOUT HOODS/HOUSING, ONLY FOR REFERENCE
不使用防护外壳时芯件的开孔安装尺寸, 仅供参考

T2040065101-000	HE-006-MSS	HE-006 MALE INSERT, DOUBLE SPRING CLAMP HE-016公插, 双弹片			
PART NUMBER 料号		PART DESCRIPTION 描述			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID WANG 01NOV2016		 TE Connectivity									
		CHK CHRIS WANG 01NOV2016											
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD XIANG XU 01NOV2016									
		0 PLC ±-		NAME HE-006-MSS									
		1 PLC ±-											
		2 PLC ±-		PRODUCT SPEC -									
		3 PLC ±-											
		4 PLC ±-		APPLICATION SPEC -									
		ANGLES ±-											
MATERIAL - -		FINISH - -		SIZE A3		CAGE CODE -		DRAWING NO C-T2040065101000		RESTRICTED TO -			
CUSTOMER DRAWING								SCALE 1:1		SHEET 1 OF 1		REV B	