




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-15-013759	27SEP2015	DW	CW
	B1	ECR-16-011988	25AUG2016	YC	CW
	B2	ECR-18-017123	10DEC2018	KW	CW
	C	ECR-21-106515	09JUL2021	SQ	CW





TYPE 1, T2040102101-000, WITH LOGO, 10X M3 SCREW, RECOMMENDED
类型 1, T2040102101-000, 带LOGO 10X M3螺丝, 推荐锁紧力矩0.5Nm




4X M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3螺丝, 推荐锁紧力矩0.5Nm

M4 SCREW, RECOMMENDED
TIGHTENING TORQUE 1.2Nm
M4螺丝, 推荐锁紧力矩1.2Nm




PANEL CUT FOR INSERTS FOR USE
WITHOUT HOODS/ HOUSINGS
不使用防护外壳时芯件的安装开孔图





NOTES:
1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 500V
RATED CURRENT: 16A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.5mm²~2.5mm² (AWG20-AWG14)
CONTACT TYPE: SCREW CLAMP (M3)




注释:
1. 技术参数:
绝缘材料: PC
额定电压: 500V
额定电流: 16A
绝缘电阻: $\geq 400M\Omega$
脉冲电压: 6KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500 次
接线范围: 0.5mm²~2.5mm² (AWG20-AWG14)
接线类型: 螺丝压接 (M3)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	GINO YAO	06APR2015	 TE Connectivity		
		CHK	CHRIS WANG	06APR2015			
		APVD	XIANG XU	06APR2015	NAME HE-010-M		
DIMENSIONS: -		TOLERANCES UNLESS OTHERWISE SPECIFIED:			PRODUCT SPEC 108-137044		
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH			APPLICATION SPEC 114-137044		
MATERIAL -		-			WEIGHT -		
					CUSTOMER DRAWING		
					SIZE A3	CAGE CODE 00779	RESTRICTED TO -
					DRAWING NO T2040102101000	SHEET 1 OF 2	REV C

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-





TYPE 2,T2040102101-001,WITHOUT LASER SIDE MARK
类型 2,T2040102101-001,不带侧面激光标识






NOTE:
ALL SPEC REFER TO TYPE 1

注释:
所有产品规范参照 TYPE 1



TYPE 3,T2049102101-000,LASER WITHOUT LOGO
类型 3,T2049102101-000,激光标识不带 LOGO



T2040102101-000	HE-010-M	HE-010 MALE INSERT HE-010 公插	TYPE 1
T2040102101-001	HE-010-M	HE-010 MALE INSERT,WITHOUT LASER SIDE MARK HE-010 公插,无激光侧面标识	TYPE 2
T2049102101-000	HE-010-M	HE-010 MALE INSERT,WITHOUT LOGO HE-010 公插,无LOGO	TYPE 3
PART NUMBER 料 号	PART DESCRIPTION 描 述		TYPE 类 型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GINO YAO 06APR2015	TE Connectivity		
		CHK CHRIS WANG 06APR2015			
DIMENSIONS: mm		APVD XIANG XU 06APR2015	NAME HE-010-M		
		PRODUCT SPEC 108-137044			
		APPLICATION SPEC 114-137044			
MATERIAL -		WEIGHT -	SIZE A3		CAGE CODE 00779
			DRAWING NO T2040102101000		RESTRICTED TO -
		CUSTOMER DRAWING	SCALE 1:1	SHEET 2 OF 2	REV C