









M4 SCREW, RECOMMENDED —
TIGHTENING TORQUE 1.2Nm
M4螺丝, 推荐扭力矩为1.2Nm

4X M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3螺丝, 推荐扭力矩为0.5Nm



PANEL CUT OUT DIMENSION FOR INSERT
WITHOUT HOODS/HOUSING, ONLY FOR REFERENCE
不使用防护外壳时芯件的开孔安装尺寸, 仅供参考

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	24NOV2016	DW	CW
	B	ECR-21-106515	21JUL2021	SQ	CW

NOTES:


I. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 500V
RATED CURRENT: 16A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: $0.5mm^2 \sim 2.5mm^2$ (AWG20-AWG14)
CONTACT FINISH: SILVER PLATED
CONTACT TYPE: DOUBLE SPRING CLAMP

注释：

1. 技术参数：

绝缘材料：	PC
额定电压：	500V
额定电流：	16A
绝缘电阻：	$\geq 400M\Omega$
脉冲电压：	6KV
污染等级：	3
阻燃等级：	UL94V-0
插拔次数：	500 次
接线范围：	$0.5mm^2 \sim 2.5mm^2$ (AWG20-AWG14)
端子表面处理：	镀银
接线类型：	双弹片连接

T2040105101-000	HE-010-MSS	HE-010 MALE INSERT,DOUBLE SPRING CLAMP HE-010公插,双弹片
PART NUMBER 料号	PART DESCRIPTION 描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 24NOV2016 DAVID WANG CHK 24NOV2016 CHRIS WANG APVD 24NOV2016 XIANG XU PRODUCT SPEC 108-137044 APPLICATION SPEC 114-137044 WEIGHT -		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		NAME HE-010-MSS	
		MATERIAL - -		FINISH - -	
		CUSTOMER DRAWING		SIZE A3	CAGE CODE -
		DRAWING NO C-T2040105101000		RESTRICTED TO -	
		SCALE 1:1		SHEET 1 OF 1	REV B