




D




PANEL CUT OUT DIMENSION FOR INSERT
WITHOUT HOODS/HOUSING, ONLY FOR REFERENCE
不使用防护外壳时芯件的开孔安装尺寸, 仅供参考


NOTES:

1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 500V
RATED CURRENT: 16A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.5mm²~2.5mm² (AWG20-AWG14)
CONTACT FINISH: SILVER PLATED
CONTACT TYPE: DOUBLE SPRING CLAMP

C



4X M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3螺丝, 推荐扭力矩为0.5Nm




M4 SCREW, RECOMMENDED
TIGHTENING TORQUE 1.2Nm
M4螺丝, 推荐扭力矩为1.2Nm


注释:

1. 技术参数:
绝缘材料: PC
额定电压: 500V
额定电流: 16A
绝缘电阻: $\geq 400M\Omega$
脉冲电压: 6KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500 次
接线范围: 0.5mm²~2.5mm² (AWG20-AWG14)
端子表面处理: 镀银
接线类型: 双弹片连接

B



A

T2040485201-000		HE-024-FSS 25-48		HE-024 FEMALE INSERT, DOUBLE SPRING CLAMP 25-48 HE-024母插, 双弹片 25-48										
PART NUMBER 料号		PART DESCRIPTION 描述												
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID WANG 30NOV2016		 TE Connectivity										
DIMENSIONS: mm		CHK CHRIS WANG 30NOV2016												
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD XIANG XU 30NOV2016			NAME HE-024-FSS 25-48							
		0 PLC ±-		PRODUCT SPEC		SIZE A2			CAGE CODE -		DRAWING NO C=T2040485201000		RESTRICTED TO B	
		1 PLC ±-		108-137044										
		2 PLC ±-		APPLICATION SPEC										
3 PLC ±-		4 PLC ±-		114-137044										
ANGLES ±-		±-												
MATERIAL - -		FINISH - -		WEIGHT -										
				CUSTOMER DRAWING		SCALE 1:1		SHEET 1 OF 1		REV B				

D

C

B

A