







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	14JUL2017	YC	CW
	B	ECR-18-015945	09OCT2018	YC	CW
	B1	ECR-19-019179	30DEC2019	YC	CW
	C	ECR-21-117384	09NOV2021	WQR	CW



M3 SCREW
RECOMMENDED TIGHTENING
TORQUE 0.5N.m
M3 螺丝，
推荐锁紧力矩0.5N.m




- NOTES:
- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 400V
RATED CURRENT: 40A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6KV
POLLUTION DEGREE: 3
MATING CYCLES: 500 CYCLES
WIRE RANGE: 1-10 mm² (18-8 AWG)
CONTACT TYPE: CRIMP CONTACT
 - CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20400X10XX000)

- 注释:
- 技术参数:
绝缘材料: PC
额定电压: 400V
额定电流: 40A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 6KV
污染等级: 3
插拔次数: 500次
接线范围: 1-10 mm² (18-8 AWG)
接线类型: 冷压接
 - 端子需要单独订购。
(订货号参考图面: T20400X10XX000)

T2080022101-000	HQ-002-M	HQ-002 MALE INSERT HQ-002 公插
PART NUMBER 产品料号	PART DESCRIPTION 产品描述	

THE CODING PINS ARE PACKAGED WITH
PRODUCT
编码销与产品一起包装出货

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 14JUL2017 YORK CHEN		TE Connectivity				
		CHK 14JUL2017 GINO YAO						
		APVD 14JUL2017 CHRIS WANG						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- ±-		NAME HQ-002-M				
				PRODUCT SPEC 108-137310				
				APPLICATION SPEC 114-137310				
				SIZE A3				
				CAGE CODE 00779				
MATERIAL - -		FINISH - -		DRAWING NO C-T2080022101000				
CUSTOMER DRAWING				SCALE 3:2		SHEET 1 OF 1		REV C