





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL	19SEP2017	YC	CW
	B1	ECR-23-181096	18JUL2023	BS	CW

NOTES:

1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 830V
RATED CURREN3T: 40A
INSULATION RESISTANCE: >=400MΩ
RATED IMPULSE VOLTAGE: 8KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 1.0~6.0mm² / 8AWG(10mm²)
CAUTION, INSULATOR OF 8AWG(10mm²) CABLE <= Ø6.1mm.
BREAK THE INSERT TO REMOVE 8AWG(10mm²) CONTACTS.

2. CONTACT TYPE: CRIMP CONTACT
CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING:T20400X10XX000)

注释:

1. 技术参数:
绝缘材料: PC
额定电压: 830V
额定电流: 40A
绝缘电阻: >=400MΩ
脉冲电压: 8KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: 1.0~6.0mm² / 8AWG(10mm²)
注意, 8AWG(10mm²) 线缆绝缘直径<= Ø6.1mm.
退出8AWG(10mm²) 针时需要破坏芯件.

2. 接线类型: 冷压接
端子需要单独订购.
(订货号参考图面: T20400X10XX000)

T2111042101-007	HMN-004-M	HMN-004 MALE MODULE INSERT HMN-004 模块公插			
PART NUMBER 料 号		PART DESCRIPTION 描 述			
DWN 19SEP2017 YORK CHEN CHK 19SEP2017 GINO YAO APVD 19SEP2017 CHRIS WANG		TE Connectivity			
PRODUCT SPEC 108-137060 APPLICATION SPEC 114-137060 WEIGHT -		NAME HMN-004-M		RESTRICTED TO -	
CUSTOMER DRAWING		SIZE A3	CAGE CODE 00779	DRAWING NO T2111042101007	REV B1
		SCALE 3:2	SHEET 1	OF 1	