

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL	19SEP2017	YC	CW

NOTES:

1. TECHNICAL CHARACTERISTICS:
 INSULATION MATERIAL: PC
 RATED VOLTAGE: 160V
 RATED CURRENT: 10A
 INSULATION RESISTANCE: $\geq 400M\Omega$
 RATED IMPULSE VOLTAGE: 2.5KV
 POLLUTION DEGREE: 2
 FLAMMABILITY: UL94V-0
 MATING CYCLES: 500 CYCLES
 WIRE RANGE: 0.14~2.5 mm² (26~14 AWG)
 CONTACT TYPE: CRIMP CONTACT

2. CONTACT NEED TO BE ORDERED SEPARATELY.
 (ORDER No. REFER TO DRAWING: T20200X20XX000)

注释:

1. 技术参数:
 绝缘材料: PC
 额定电压: 160V
 额定电流: 10A
 绝缘电阻: $\geq 400M\Omega$
 额定脉冲电压: 2.5KV
 污染等级: 2
 阻燃等级: UL94V-0
 插拔次数: 500次
 接线范围: 0.14~2.5 mm² (26~14 AWG)
 接线类型: 冷压接

2. 端子需要单独订购.
 (订货号参考图面: T20200X20XX000)

T2111172201-007	HMN-017-F	HMN-017 FEMALE MODULE INSERT HMN-017模块母插	
PART NUMBER 料号		PART DESCRIPTION 描述	
DWN 19SEP2017 YORK CHEN			
CHK 19SEP2017 GINO YAO			
APVD 19SEP2017 CHRIS WANG		NAME HMN-017-F	
PRODUCT SPEC 108-137062		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
APPLICATION SPEC 114-137062		A300779 © T2111172201007 -	
WEIGHT -		SCALE 3:2 SHEET 1 OF 1 REV B	
Customer Drawing			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±-

MATERIAL

-

FINISH

-

1470-19 (3/13)