

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20


BY -

ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	12JUL2016	RL	CW
	A1	ECR-17-009384	25DEC2017	RL	CW


ASSEMBLY STATE OF THE PRODUCT, FOR REFERENCE
产品装配状态, 供参考





M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5 Nm
M3螺丝, 推荐锁紧力矩 0.5 Nm



FOR Ø3-6mm CABLE
用于直径Ø3-6mm 电缆线



FOR Ø6-9.5mm CABLE
用于直径Ø6-9.5mm 电缆线



SCALE 3:2

- NOTES:
- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 50 V
RATED CURRENT: 10 A
RATED IMPULSE VOLTAGE: 0.8 KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)
CONTACT TYPE: CRIMP CONTACT
 - CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20200X10XX000)

- 注释:
- 技术参数:
绝缘材料: PC
额定电压: 50V
额定电流: 10A
额定脉冲电压: 0.8kV
污染等级: 3
阻燃等级: UL94V-0
接线范围: 0.14-2.5 mm² (26-14 AWG)
接线类型: 冷压接
 - 端子需要单独订购.
(订货号参考图面: T20200X10XX000)

T2580011154-001

PIN-Q2-M1

QUINTAX MALE CONTACT 1-POS, 10A
QUINTAX 1-POS公针, 10A

PART NUMBER
料号

PART DESCRIPTION
描述

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN ROY LIU 12JUL2016

CHK KYLE ZENG 12JUL2016

APVD CHRIS WANG 12JUL2016

PRODUCT SPEC

108-137067

APPLICATION SPEC


114-137067

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:

mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL

-

FINISH

-



TE Connectivity

NAME
QUINTAX MALE CONTACT 1-POS, 10A
PIN-Q2-M1

SIZE

A3

CAGE CODE

-

DRAWING NO

©-T2580011154001

RESTRICTED TO

-

SCALE

2:1

SHEET

1 OF 1

REV

A1