


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	12JUL2016	RL	CW
	A1	ECR-17-009384	25DEC2017	RL	CW

ASSEMBLY STATE OF THE PRODUCT, FOR REFERENCE
产品装配状态, 供参考




- NOTES:
- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 50 V
RATED CURRENT: 10 A
RATED IMPULSE VOLTAGE: 0.8 kV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)
CONTACT TYPE: CRIMP CONTACT
 - CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20200X20XX000)

- 注释:
- 技术参数:
绝缘材料: PC
额定电压: 50V
额定电流: 10A
额定脉冲电压: 0.8kV
污染等级: 3
阻燃等级: UL94V-0
接线范围: 0.14-2.5 mm² (26-14 AWG)
接线范围: 冷压接
 - 端子需要单独订购.
(订货号参考图面: T20200X20XX000)

FOR Ø3-6mm CABLE
用于直径Ø3-6mm 电缆线

FOR Ø6-9.5mm CABLE
用于直径Ø6-9.5mm 电缆线



SCALE 3:2

T2580012154-001	PIN-Q2-F1	QUINTAX FEMALE CONTACT 1-POS, 10A QUINTAX 1-POS母针, 10A
PART NUMBER 料号	PART DESCRIPTION 描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ROY LIU 12JUL2016	 TE Connectivity		
DIMENSIONS: mm		CHK KYLE ZENG 12JUL2016			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD CHRIS WANG 12JUL2016			
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-137067			
MATERIAL -		APPLICATION SPEC 114-137067	NAME QUINTAX FEMALE CONTACT 1-POS, 10A PIN-Q2-F1		
FINISH -		WEIGHT -	SIZE A3	CAGE CODE -	DRAWING NO T2580012154001
CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 1	REV A1	RESTRICTED TO -