

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	12DEC2017	YC	CW
	A1	ECR-18-018540	07DEC2018	AL	CW

ASSEMBLY STATE OF THE PRODUCT, FOR REFERENCE

产品装配状态, 供参考

M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5 N.m
M3螺丝, 推荐锁紧力矩0.5 N.m

NOTES:

- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 50V
RATED CURRENT: 10A
RATED IMPULSE VOLTAGE: 0.8KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)
CABLE DIAMETER: 3 - 9.5 mm
CONTACT TYPE: CRIMP CONTACT
- CONTACT NEED TO BE ORDERED SEPARATELY.

注释:

- 技术参数:
绝缘材料: PC
额定电压: 50V
额定电流: 10A
额定脉冲电压: 0.8KV
污染等级: 3
阻燃等级: UL94V-0
接线范围: 0.14-2.5 mm² (26-14 AWG)
电缆外径: 3-9.5 mm
接线类型: 冷压接
- 端子需要单独订购.

FOR Ø6-9.5mm CABLE
用于直径 Ø6-9.5mm 电缆线

FOR Ø3-6mm CABLE
用于直径 Ø3-6mm 电缆线

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±-
MATERIAL	FINISH
-	-
-	-

DWN	22DEC2017
YORK CHEN	
CHK	22DEC2017
GINO YAO	
APVD	22DEC2017
CHRIS WANG	
PRODUCT SPEC	108-137067
APPLICATION SPEC	114-137067
WEIGHT	-
CUSTOMER DRAWING	

T2580032154-007	PIN-Q2-F	QUINTAX FEMALE CONTACT 4-POS QUINTAX 4-POS 母针
-----------------	----------	--

PART NUMBER	PART DESCRIPTION
料号	描述

NAME
QUINTAX CONTACT 4-POS
PIN-Q2-F

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	©-T2580032154007	-

SCALE	SHEET	OF	REV
2:1	1	1	A1

1470-19 (3/13)