

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	17JUL2017	QY	CW
	A1	ECR-17-011829	16AUG2017	QY	CW

NOTE:  
 1. TECHNICAL CHARACTERISTICS:  
 LOCK MATERIAL : POLYAMIDE  
 BODY MATERIAL : POLYAMIDE  
 SEAL MATERIAL : RUBBER  
 CLAMPING RANGE : SEE TABLE  
 TEMPERATURE RANGE : -40~+115°C  
 PROTECTION DEGREE : IP66 (MATED)

注释:  
 1. 技术参数:  
 内锁扣材料: 尼龙  
 主体材料: 尼龙  
 密封材料: 橡胶  
 夹线范围: 见表格  
 工作温度: -40~+115°C  
 防护等级: IP66 (配合)

T3541403502-000	WQWI-M40B/AD34.5-0	PLASTIC RIGHT ANGLED FLEXIBLE TUBE FITTINGS M40 (AD34.5), BLACK 塑料软管接头 M40 (AD34.5), 黑色	M40X1.5	AD34.5	15	44	42.5	70.5	65.5
T3541404302-000	WQWI-M40B/AD42.5-0	PLASTIC RIGHT ANGLED FLEXIBLE TUBE FITTINGS M40 (AD42.5), BLACK 塑料软管接头 M40 (AD42.5), 黑色	M40X1.5	AD42.5	15	52	55.5	81	73.5
PART NUMBER 料号	PART DESCRIPTION 零件描述	PG/M THREAD PG/M 螺纹	FITS TO TUBING SIZE AD 适配软管AD	GL(mm) 螺纹长度(mm)	ØD(mm) 外形直径(mm)	ØB(mm) 外形直径(mm)	(E)	H	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:  
ACC. to ISO 2768-M

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±

MATERIAL

FINISH

DWN 17JUL2017

QIANG YUAN

CHK 17JUL2017

GINO YAO

APVD 17JUL2017

CHRIS WANG

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

NAME  
PLASTIC RIGHT ANGLE FLEXIBLE TUBE FITTINGS

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-T3541XXXX0X000

SCALE

1:1

SHEET

OF

1

REV

A1

1470-19 (3/13)