

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	22JUN2017	DW	CW

WIRE RANGE

M40X 1.5

(34)

9

50

Ø55

NOTES / 注解:

I. TECHNICAL CHARACTERISTICS / 技术参数:

SHELL MATERIAL / 主体材料 : NICKEL PLATED BRASS / 铜镀镍

SEAL MATERIAL / 密封材料: RUBBER, BLACK

PINCH RING MATERIAL / 夹紧件材料: NYLON, GREY

OPERATION TEMPERATURE / 工作温度: -40°C - +100°C

PROTECTION DEGREE / 防护等级: IP68

WIRE RANGE / 夹线范围: 22-32 mm

T3706400103-000

DLX-40-MC (22-32)
电磁屏蔽金属接头 M40 (22~32)PART NUMBER
料号PART DESCRIPTION
描述

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 22JUN2017

DAVID WANG

CHK 22JUN2017

GINO YAO

APVD 22JUN2017

CHRIS WANG

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±-

MATERIAL

-

FINISH

-

TE Connectivity

NAME
DLX-40-MC (22-32)

SIZE

A3

CAGE CODE

-

DRAWING NO

T3706400103000

RESTRICTED TO

-

SCALE

1:1

SHEET

1 OF 1

REV

A

1470-19 (3/13)