

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	25JUL2016	DW	CW

SCALE 1:1

WIRE RANGE

M20X 1.5

(23.2)

6.5

Ø26.6

SW24

NOTES / 技术指标:

I. TECHNICAL CHARACTERISTICS / 技术参数:

SHELL MATERIAL / 主体材料: NICKEL PLATED BRASS / 铜镀镍

SEAL MATERIAL / 密封材料: NBR / 丁腈橡胶

PINCH RING MATERIAL / 夹紧件材料: PA / 尼龙塑料

OPERATION TEMPERATURE / 工作温度: -40°C - +100°C

PROTECTION DEGREE / 防护等级: IP68

WIRE RANGE / 夹线范围: 5-9 mm

T3707200113-000

DLX-20-MTC (5-9)  
电磁屏蔽金属接头(M20)(5-9)PART NUMBER  
料号PART DESCRIPTION  
描述

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±-

MATERIAL

FINISH

DWN 25JUL2016

DAVID WANG

CHK 25JUL2016

CHRIS WANG

APVD 25JUL2016

XIANG XU

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

NAME  
DLX-20-MTC (5-9)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

G-T3707200113000

SCALE  
2:1SHEET  
1 OF 1REV  
A

1470-19 (3/13)