

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -






ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	03MAY2017	DW	CW

NOTES / 注解:

I. TECHNICAL CHARACTERISTICS / 技术参数:
SHELL MATERIAL / 主体材料 : NICKEL PLATED BRASS / 铜镀镍
SEAL MATERIAL / 密封材料: RUBBER, BLACK
PINCH RING MATERIAL / 夹紧件材料: NYLON, GREY
OPERATION TEMPERATURE / 工作温度: -40°C - +100°C
PROTECTION DEGREE / 防护等级: IP68
WIRE RANGE / 夹线范围: 37-44 mm



T3707630103-000


DLX-63-MC (37~44)
电磁屏蔽金属接头 M63 (37~44)

PART NUMBER
料 号

PART DESCRIPTION
描 述

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL

FINISH

DWN 03MAY2017

DAVID WANG

CHK 03MAY2017

CHRIS WANG

APVD 03MAY2017

XIANG XU

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME
DLX-63-MC (37-44)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

-

© T3707630103000

-

SCALE

1:2

SHEET

1 OF 1

REV

A