

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	01.04.2020	SI	SI

# TAMPER-PROOF LABELS OVERVIEW



SERIES	PART NO.	DESCRIPTION	MATERIAL	TTDS
MV	E27427-000	MV-254064-10-8A	SV7000, Polyester silver (0,077 mm), Acrylic adhesive with „VOID“ Pattern	TTDS-084






Quantity per roll: 10.000 PCs

Labels across: 3

Winding: outside

length of roll: 31,8 m



LABEL BUILD DETAILS		TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT		DWN S. Iser / 01.04.2020 DATE		TE Connectivity	
 SUBSTRATE	LABEL HEIGHT:	±0,3	[.012]	 DIMENSIONS mm [INCHES] TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH	CHK S. Iser / 01.04.2020 DATE				
 ADHESIVE	LABEL WIDTH:	±0,3	[.012]		APVD S. Iser / 01.04.2020 DATE				
 LINER	WEB WIDTH:	±0,8	[.031]		PRODUCT SPEC DATE	Tamper-proof Label Size „254064“			
	VERTICAL REPEAT:	±0,8	[.031]*		APPLICATION SPEC DATE	WEIGHT 0,016 g			
	HORIZONTAL REPEAT:	±0,8	[.031]*			SIZE A3 CAGE CODE C2290 DRAWING NO. C-TAMPER-PROOF RESTRICTED TO			
	PRINT POSITIONING:	±0,8	[.031]*			CUSTOMER DRAWING SHEET 1 of 1 REV A1			
	LEFT MARGIN:	±0,4	[.016]						
	QUANTITY:	-0% +2%							
	*NON ACCUMULATING								

All dimensions in mm [inch]

labels are centered on the liner as long as not declared separately

TAMPER-PROOF SERIES