




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	01.04.2020	SI	SI

# TAMPER-PROOF LABELS OVERVIEW

SERIES	PART NO.	DESCRIPTION	MATERIAL	TTDS
MV	C07219-000	MV-318097-10-8A	SV7000, Polyester silver (0,077 mm), Acrylic adhesive with „VOID“ Pattern	TTDS-084
TN	D67328-000	TN-318097-10-9	PE7021, Polyethylene destructive white matt (0,07 mm), Acrylic adhesive	TTDS-091

Quantity per roll:   
 Labels across:   
 Winding:   
 length of roll:



LABEL BUILD DETAILS		TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT		DWN S. Iser / 01.04.2020 DATE		TE Connectivity			
SUBSTRATE	LABEL HEIGHT:	±0,3 [0,012]		DIMENSIONS mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED	CHK S. Iser / 01.04.2020 DATE	APVD S. Iser / 01.04.2020 DATE	Name			
ADHESIVE	LABEL WIDTH:	±0,3 [0,012]				Tamper-proof Label Size „318097“					
LINER	WEB WIDTH:	±0,8 [0,031]		 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	MATERIAL SEE TABLE FINISH	PRODUCT SPEC DATE	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
	VERTICAL REPEAT:	±0,8 [0,031]*				WEIGHT	A3	C2290	C-TAMPER-PROOF		
	HORIZONTAL REPEAT:	±0,8 [0,031]*				MV: 0,038 g   TN: 0,031 g	CUSTOMER DRAWING		SHEET	1 of 1	REV A1
	PRINT POSITIONING:	±0,8 [0,031]*									
	LEFT MARGIN:	±0,4 [0,016]									
	QUANTITY:	-0% +2%									
		*NON ACCUMULATING									

All dimensions in mm [inch]  
 labels are centered on the liner  
 as long as not declared separately

TAMPER-PROOF SERIES