



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	01.04.2020	SI	SI

# TAMPER-PROOF LABELS OVERVIEW

SERIES	PART NO.	DESCRIPTION	MATERIAL	TTDS
MV	E94126-000	MV-381127-5-8A	SV7000, Polyester silver (0,077 mm), Acrylic adhesive with „VOID“ Pattern	TTDS-084
TN	D01421-000	TN-381127-5-9	PE7021, Polyethylene destructive white matt (0,07 mm), Acrylic adhesive	TTDS-091

Quantity per roll:   
 Labels across:   
 Winding:   
 length of roll:



Color-appearance on roll



All dimensions in mm [inch]  
 labels are centered on the liner  
 as long as not declared separately

LABEL BUILD DETAILS	TOLERANCES mm [INCH]	THIS DRAWING IS A CONTROLLED DOCUMENT	DWN	DATE	TE Connectivity				
SUBSTRATE	LABEL HEIGHT: ±0,3 [0,12]	DIMENSIONS mm [INCHES] TOLERANCES UNLESS OTHERWISE SPECIFIED 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	S. Iser / 01.04.2020	DATE					
ADHESIVE	LABEL WIDTH: ±0,3 [0,12]		CHK	S. Iser / 01.04.2020					DATE
LINER	WEB WIDTH: ±0,8 [0,31]		APVD	S. Iser / 01.04.2020	DATE	Name			
	VERTICAL REPEAT: ±0,8 [0,31]*		PRODUCT SPEC		DATE	Tamper-proof Label Size „381127“			
	HORIZONTAL REPEAT: ±0,8 [0,31]*		APPLICATION SPEC		DATE				
	PRINT POSITIONING: ±0,8 [0,31]*		WEIGHT	MV: 0,057 g   TN: 0,048 g		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	LEFT MARGIN: ±0,4 [0,16]					A3	C2290	C-TAMPER-PROOF	
	QUANTITY: -0% +2%		CUSTOMER DRAWING		SHEET 1 of 1		REV A1		
	*NON ACCUMULATING								

TAMPER-PROOF SERIES