

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	01.04.2020	SI	SI

# TAMPER-PROOF LABELS OVERVIEW


SERIES	PART NO.	DESCRIPTION	MATERIAL	TTDS
MV	E47442-000	MV-699191-5-8A	SV7000, Polyester silver (0,077 mm), Acrylic adhesive with „VOID“ Pattern	TTDS-084
TN	D14042-000	TN-699191-5-9	PE7021, Polyethylene destructive white matt (0,07 mm), Acrylic adhesive	TTDS-091

Quantity per roll: 5.000 PCs

Labels across: 1

Winding: outside

length of roll: 111,3 m



approx. Ø 167-172 [6.575-6.772]

Ø 76,2 [3,00]

Color-appearance on roll

TN white

MV silver

### LABEL BUILD DETAILS

	SUBSTRATE
	ADHESIVE
	LINER

### TOLERANCES mm [INCH]

LABEL HEIGHT:	±0,3 [0,12]
LABEL WIDTH:	±0,3 [0,12]
WEB WIDTH:	±0,8 [0,31]
VERTICAL REPEAT:	±0,8 [0,31]*
HORIZONTAL REPEAT:	±0,8 [0,31]*
PRINT POSITIONING:	±0,8 [0,31]*
LEFT MARGIN:	±0,4 [0,16]
QUANTITY:	-0% +2%
*NON ACCUMULATING	

### THIS DRAWING IS A CONTROLLED DOCUMENT

DIMENSIONS mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
ANGLES	± -
MATERIAL	FINISH
SEE TABLE	

DWN	S. Iser / 01.04.2020	DATE
CHK	S. Iser / 01.04.2020	DATE
APVD	S. Iser / 01.04.2020	DATE
PRODUCT SPEC		DATE
APPLICATION SPEC		DATE
WEIGHT	MV: 0,160 g   TN: 0,133 g	



Name  
Tamper-proof Label Size „699191“

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	C2290	C-TAMPER-PROOF	

CUSTOMER DRAWING

SHEET 1 of 1 REV A1

All dimensions in mm [inch]

labels are centered on the liner as long as not declared separately

TAMPER-PROOF SERIES