



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	29.04.2020	SI	SI

Single Marker

Sheet Layout



Quantity per sheet: 3 PCs  
 Sheets in envelope: 10 SH  
 Total PCs: 30 PCs

Final Presentation Envelope

Clear gloss self-laminating area. Light blue color only for indication of area

TE PN: 6-1768048-2

All dimensions in mm [inch]

LABEL BUILD DETAILS	
	PRINT
	SUBSTRATE
	ADHESIVE
	LINER

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0,3 [0,12]
LABEL WIDTH:	±0,3 [0,12]
WEB WIDTH:	±0,8 [0,31]
VERTICAL REPEAT:	±0,8 [0,31]*
HORIZONTAL REPEAT:	±0,8 [0,31]*
PRINT POSITIONING:	±0,8 [0,31]*
LEFT MARGIN:	±0,4 [0,16]
QUANTITY:	-0% +2%
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT

DIMENSIONS mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED	
	0 PLC	±	±
	1 PLC	±	±
	2 PLC	±	±
	3 PLC	±	±
4 PLC	±	±	±
ANGLES		±	±

MATERIAL: SEE TABLE  
 FINISH: GLOSS UNPRINTED MATT PRINTED

PRINT	Screen-Print in 1-color white		
MATERIAL	PV004, SOFT-PVC clear gloss (0,05 mm)		
ADHESIVE TYP	Acrylic permanent (0,02 mm)		
LINER	Kraft white (0,145 mm)		
DWN	S. Iser / 29.04.2020	DATE	
CHK	S. Iser / 29.04.2020	DATE	
APVD	S. Iser / 29.04.2020	DATE	
PRODUCT SPEC	DATE		
APPLICATION SPEC	DATE		
WEIGHT	0,120 g		
SIZE	A3	CAGE CODE	C2290
DRAWING NO	6-1768048-2		RESTRICTED TO
CUSTOMER DRAWING		SHEET	1 of 1
		REV	A1

6-1768048-2