



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	13JUN2023	BDA	MB

PART AS SUPPLIED



PART FULLY RECOVERED



PRODUCT DIMENSIONS

PART NUMBER	AS SUPPLIED		AS RECOVERED							
	D MINIMUM		A MAXIMUM		B MINIMUM		C		E NOMINAL	
	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.
TPEM-NR502	2.70	0.106	2.16	0.085	0.90	0.035	7.30±0.50	0.287±0.020	1.90	0.075


PRODUCT INFORMATION

1. FLAME RETARDED
2. HEAT-SHRINKABLE, THERMALLY STABILISED, IRRADIATED, POLYOLEFIN
3. STANDARD SUPPLIED LENGTH: 1.2 METRES
4. COLOUR: BLACK
5. TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING

STANDARD CUTTING TOLERANCES (mm)	
CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm(inches)



MATERIAL SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±0.1
3 PLC	±0.01
4 PLC	±0.001
ANGLES	±
FINISH	-

DWN	13JUN2023	BASAVARAJA D A
CHK	13JUN2023	SELVAPANDIAN B
APVD	13JUN2023	MAYO BAKARE
PRODUCT SPEC	RK-6029	
APPLICATION SPEC	-	
WEIGHT	-	
CUSTOMER DRAWING		

NAME TPEM-NR502



SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	©-TPEMNR502	-
SCALE NTS		SHEET 1 OF 1	REV A