



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING FORMAT	08MAY2020	GK	DB

### LABEL AND LINER DESIGN



### PRESENTATION



**OUTSIDE WOUND (BACK SLIT LEFT)**  
**LABEL ACROSS: 1**  
**PER ROLL QTY: 30.48m / 100 feet**

All dimensions in mm [Inch]

**TE PN: 318606-000**

<b>TOLERANCES mm [INCH]</b> LABEL HEIGHT: ±0.3 [0.012] LABEL WIDTH: ±0.3 [0.012] WEB WIDTH: ±0.8 [0.031] VERTICAL REPEAT: ±0.8 [0.031]* HORIZONTAL REPEAT: ±0.8 [0.031]* PRINT POSITIONING: ±0.8 [0.031]* LEFT MARGIN: ±0.4 [0.016] QUANTITY: -0 % +2 % *NON ACCUMULATING		THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm [INCHES] TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		DWN: GOPALAKRISHNA HV 08MAY2020 CHK: D.BURGAT 08MAY2020 APVD: D.BURGAT 08MAY2020 PRODUCT SPEC: TTDS-005 APPLICATION SPEC: -		MATERIAL: POLYVINYL FLUORIDE (TEDLAR®) ADHESIVE TYPE: PERMANENT ACRYLIC LINEAR: BROWN KRAFT		NAME: TEDLAR® LABEL - YELLOW - CONTINUOUS 19.1mm x 30.4m (0.75inch x 100ft)		SIZE: A2 CAGE CODE: FB1U7 DRAWING NO: C=TTVF075YW-100 RESTRICTED TO: -	
MATERIAL: SEE TABLE		FINISH: GLOSS		WEIGHT: 80g		SCALE: NTS		SHEET: 1 of 1		REV: A1	