



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING FORMAT	08MAY2020	GK	DB

LABEL AND LINER DESIGN



PRESENTATION



All dimensions in mm [Inch]

TE PN: 412200-000

OUTSIDE WOUND (BACK SLIT LEFT)
LABEL ACROSS: 1
PER ROLL QTY: 30.48m / 100 feet

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±
MATERIAL SEE TABLE	FINISH GLOSS

MATERIAL ADHESIVE TYPE LINEAR		POLYVINYL FLUORIDE (TEDLAR®) PERMANENT ACRYLIC BROWN KRAFT	
DWN GOPALAKRISHNA HV 12MAY2020	CHK D.BURGAT 12MAY2020	APVD D.BURGAT 12MAY2020	
PRODUCT SPEC TTDS-005		NAME TEDLAR® LABEL – YELLOW – CONTINUOUS 38.1mm x 30.4m (1.5inch x 100ft)	
APPLICATION SPEC —		SIZE A2	RESTRICTED TO —
WEIGHT 159g		CAGE CODE FB1U7	DRAWING NO TTVF150YW-100
CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 1
		REV A1	