

Product Construction: 10 Conductor Cable Jacketed		REDRAWN 29/10/02	Product Description VG 95218 T027 A003 (EPD87257*)	Issue A ① S'sedes
Designer Colin Aldridge	Date 13/08/1997	Product Manager Dave Gardner	Date 03/06/1999	Page 1 of 1
			Controlled Customer Copy BWB GERMANY	
			Specifications VG 95218 Part 27 Type A ①	
			<p>The copyright in this drawing is the property of Tyco Electronics UK Limited. The drawing is issued on condition it is not copied, reproduced or disclosed to a third party either in whole or in part without prior written consent of Tyco Electronics UK Limited.</p>	
Layer Type / Operation	Component Details <small>Part Numbers refer to issue in effect at date of issue of this EPD.</small>		Nominal O.D.mm	
Components: Wire	10 of VG 95218-T020-E089- Numbers as above			
Cabling: Layer 1 Layer 2	2 of VG 95218-T020-E089 8 of VG 95218-T020-E089		8.3	
Wrap:	Mylar		8.4	
Jacket: Extrusion 1	Zerohal* - Black. Marked 'Raychem - VG 95218 T027 A003 - K1010 - VG Reg.Nr. 7094' ①		10.5 ±0.3 0.84mm minimum wall ①	
	① CR02-TP-0174 refers to changes.29/10/02. J.C.			
Maximum Surface Transfer Impedance	Notes		Calculated maximum ①	
	* - Raychem Trademark		224	

If printed this document is an uncontrolled copy and reflects the issue status of the document on 26/10/2005 22:17

Lengths: Unless otherwise specified on your order this cable may be supplied in the following maximum number of continuous lengths:

Order Quantity (m) + One other length
100

Tyco Electronics UK Ltd
Faraday Road, Dorcan
Swindon SN3 5HH
Tel: (01793) 528171
Telex: 449409

Registration Number:
550926 London, England