



P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL RELEASE	26FEB2020	GK	MN

LABEL AND LINER DESIGN



PRESENTATION



All dimensions in mm [Inches]

TE PN: C11336-000

**OUTSIDE WOUND
LABEL ACROSS: 1
PER ROLL QTY: 2500**


MATERIAL	WHITE POLYESTER
ADHESIVE TYPE	PERMANENT
LINER	GLASSINE PAPER

3.0 [.118]

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
FINISH	-

MATERIAL
SEE TABLE

DWN	20FEB2020
CHK	GOPALAKRISHNA HV
APVD	20FEB2020
PRODUCT SPEC	M.NUTTALL
APPLICATION SPEC	M.NUTTALL
WEIGHT	TTDS-073
	0.581g

STE TE Connectivity

WP - WHITE POLYESTER LABELS

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	C2290	C-WP-101635-2.5-9	-

CUSTOMER DRAWING SCALE NTS SHEET 1 OF 1 REV B