



P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-20-003872	13MAR2020	GK	MN

LABEL AND LINER DESIGN



PRESENTATION



All dimensions in mm [Inches]

TE PN: D41432-000

**OUTSIDE WOUND
LABEL ACROSS: 1
PER ROLL QTY: 10000**

MATERIAL	WHITE POLYESTER
ADHESIVE TYPE	PERMANENT
LINER	GLASSINE PAPER

TOLERANCES mm [INCH]	
LABEL HEIGHT:	± 0.3 [.012]
LABEL WIDTH:	± 0.3 [.012]
WEB WIDTH:	± 0.8 [.031]
VERTICAL REPEAT:	± 0.8 [.031]*
HORIZONTAL REPEAT:	± 0.8 [.031]*
PRINT POSITIONING:	± 0.8 [.031]*
LEFT MARGIN:	± 0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm [INCHES]			
	0 PLC	\pm	-
	1 PLC	\pm	-
	2 PLC	\pm	-
	3 PLC	\pm	-
	4 PLC	\pm	-
ANGLES		\pm	-
FINISH			
MATERIAL		SEE TABLE	

DWN	20JAN2008	GOPALAKRISHNA HV
CHK	20JAN2008	K. MUNZ
APVD	20JAN2008	K. MUNZ
PRODUCT SPEC	TTDS-073	
APPLICATION SPEC		
WEIGHT	0.018g	

TE Connectivity		NAME		WP - WHITE POLYESTER LABELS	
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
A3	C2290	G-WP-318064-10-9	-		
CUSTOMER DRAWING		SCALE	SHEET	REV	
		NTS	1 OF 1	B	