



P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL RELEASE	24FEB2020	GK	MN

LABEL AND LINER DESIGN



PRESENTATION



All dimensions in mm [Inches]

TE PN: A51165-000

**OUTSIDE WOUND
LABEL ACROSS: 1
PER ROLL QTY: 10000**

MATERIAL	WHITE POLYESTER
ADHESIVE TYPE	PERMANENT
LINER	GLASSINE PAPER

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
MATERIAL SEE TABLE	FINISH -

DWN	28FEB2007
GOPALAKRISHNA HV	
CHK	20FEB2020
M.NUTTALL	
APVD	20FEB2020
M.NUTTALL	
PRODUCT SPEC	
TTDS-073	
APPLICATION SPEC	
WEIGHT	0.028g

TE Connectivity		NAME		RESTRICTED TO	
		WP - WHITE POLYESTER LABELS		-	
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
A3	C2290	G-WP-318097-10-9	-		
CUSTOMER DRAWING		SCALE	SHEET	REV	
		NTS	1 OF 1	B	