



P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-20-003872	14OCT2020	MN	AK

### LABEL AND LINER DESIGN

### PRESENTATION



All dimensions in mm [Inches]

**TE PN: D91401-000**

**OUTSIDE WOUND  
LABEL ACROSS: 1  
PER ROLL QTY: 2500**

MATERIAL	WHITE POLYESTER
ADHESIVE TYPE	PERMANENT
LINER	GLASSINE PAPER

3.0 [.118]

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm [INCHES]	
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
	ANGLES ± -
	FINISH ± -

DWN	25JUL2007
CHK	GOPALAKRISHNA HV
APVD	14OCT2020
APVD	M. NUTTALL
APVD	14OCT2020
APVD	A. KEAN
PRODUCT SPEC	TTDS-073
APPLICATION SPEC	
WEIGHT	0.261g

TE Connectivity	
NAME	
WP - WHITE POLYESTER LABELS	
SIZE	CAGE CODE
A3	C2290
DRAWING NO	RESTRICTED TO
G-WP-762381-2.5-9	-
SCALE	SHEET
NTS	1 OF 1
REV	B