



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	25SEP2020	GK	DB

### LABEL AND LINER DESIGN



### PRESENTATION



All dimensions in mm [Inches]

**TE PN: CT92183001**

**OUTSIDE WOUND  
LABEL ACROSS: 1  
PER ROLL QTY: 2500**

MATERIAL	WHITE POLYESTER
ADHESIVE TYPE	ACRYLIC PERMANENT
LINER	WHITE GLASSINE

TOLERANCES mm [INCH]	
LABEL HEIGHT:	$\pm 0.3$ [.012]
LABEL WIDTH:	$\pm 0.3$ [.012]
WEB WIDTH:	$\pm 2.0$ [.079]
VERTICAL REPEAT:	$\pm 0.8$ [.031]*
HORIZONTAL REPEAT:	$\pm 0.8$ [.031]*
PRINT POSITIONING:	$\pm 0.8$ [.031]*
LEFT MARGIN:	$\pm 0.7$ [.027]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm [INCHES]			
	0 PLC	$\pm$	-
	1 PLC	$\pm$	-
	2 PLC	$\pm$	-
	3 PLC	$\pm$	-
	4 PLC	$\pm$	-
	ANGLES	$\pm$	-
MATERIAL		FINISH	
SEE TABLE		-	

DWN	25SEP2020
GOPALAKRISHNA HV	
CHK	25SEP2020
D. BURGAT	
APVD	25SEP2020
D. BURGAT	
PRODUCT SPEC	
TTDS-301	
APPLICATION SPEC	
WEIGHT	0.312g

		TE Connectivity	
		NAME	
White Polyester Chemical Resistant -		61.0 x 41.9mm [2.4 x 1.65inch]	
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	FB1U7	C=WPCR-610419-2.5-9	-
CUSTOMER DRAWING		SCALE	SHEET
		NTS	1 OF 1
		REV	A