BUCHANAN WireMate CONNECTORS

Slim Poke-In Series

TE Connectivity (TE)'s BUCHANAN WireMate connector slim pokein series are developed for wire to PCB board connection. The slim connector with no housing serves as an easy poke-in connector with strong retention ability. The advantage of using this connector is that the conductor can be connected quickly without special tools and the small profile saves the space on the PCB.



Applications

- LED Lighting Systems
- Home Automation
- Security Systems
- Telecommunications

Electrical

Voltage rating: 300 VAC MaxDielectric strength: 2000 VAC

Specification

Application Specification: <u>114-137049</u>
Product Specification: <u>108-137049</u>
UL Approval: UL1977

Materials

• Contact: Copper Alloy with Tin plating

Mechanical

Operating temperature range -40 to 125°C
Wire retention: 30 N Minimum
Current rating: see table below

Benefits

- Quick solderless poke in connector design
- · Slim contacts that have no covering housing
- Several solutions for solid and stranded wire from 16 AWG to 24 AWG
- Safety standards with UL/CQC approval
- Available in Tape & Reel packaging

Current Ratings						
Part number	16 AWG	18 AWG	20 AWG	22 AWG	24 AWG	
2834010-3	-	-	11 A	8 A	6 A	
2834012-3	16 A	13 A	11 A	-	-	





Product Selection Information


Description	Part Number		
For wire 20, 22 and 24 AWG	2834010-3		
For wire 16, 18 and 20 AWG	2834012-3		


Dimensions

2834010-3













2834012-3





RECOMMENDED PCB LAYOUT





Dimensions are shown for reference purposes only. Specifications subject to change.

te.com

© 2017 TE Connectivity. All Rights Reserved. BUCHANAN, TE, TE Connectivity, and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other logos, product and Company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims via ill implied warranties regarding the information contained herein, including, but inlined to, any implied warranties of merchantalities of merchantalities of merchantality or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

1-1773869-6 JN 6/2017

USA: +1 (800) 522-6752 Canada: +1 (905) 475-6222 Mexico: +52 (0) 55-1106-0800 Latin/S. America: +54 (0) 11-4733-2200 Germany: +49 (0) 6251-133-1999 UK: +44 (0) 800-267666 France: +33 (0) 1-3420-868 The Netherlands: +31 (0) 73-6246-999 China: +86 (0) 400-820-6015

