SOLARLOK MEDIUM JUNCTION BOX

SMART PCB ENCLOSURE

The SOLARLOK Medium Smart Junction Box enables the integration of a Printed Circuit Board into the solution. The enclosure (junction box itself with no PCB*) is TUV and UL approved. Special clips allow you to quickly and reliably connect your PCB to the solar panel foils.



*Junction box is supplied with no printed circuit board.

Applications

Solar panels

Electrical

 Rated Voltage (Junction Box):

1000 / 1500 (UL)

1000 / 1500 (TUV) IEC and UL have to be

approved separately depending

upon the PCB enclosed

• Rated Current: Depends on the designed

electronics of the pcb

Mechanical

• Operating Temperature: $-40~^{\circ}\text{C}$ to 90 $^{\circ}\text{C}$

• Protection degreed: IP 65/67

Specifications

Application Specification: 114-13303-1
Product Specification: 108-133063
Instruction Sheet: 408-133063

• RoHS & REACH compliant

Materials

- $\bullet \ \textbf{Polyphenyl Ether} \ (\texttt{PPE})$
- Polystyrene (PS)


Benefits

- Enclosing a PCB enables:
 - Monitoring the functionality of your Junction Box
 - Adapting your Junction Box to meet changing conditions
 - Shutting down remotely when required



Product Selection Information

Part Number	Description	Cable Length (Millimeters)
2176829-1	Medium Smart PCB JBox	1000mm
2176829-2	Medium Smart PCB JBox	2700mm
2176829-3	Medium Smart PCB JBox	1000mm
2176829-4	Medium Smart PCB JBox	680mm



te.com

© 2016 TE Connectivity. All Rights Reserved. SOLARLOK, TE Connectivity, TE and TE connectivity (logo) are trademarks. Other logos, product and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

1-1773882-5 JN 6/2016

USA: +1 (800) 522-6752 Canada: +1 (905) 475-6222 Mexico: +52 (0) 55-1106-0800 Latin/S. America: +54 (0) 11-4733-2200 Germany: +49 (0) 6251-133-1999 UK: +44 (0) 800-267666 France: +33 (0) 1-3420-8686 The Netherlands: +31 (0) 73-6246-999 China: +86 (0) 400-820-6015

