LUMAWISE DIMMING RECEPTACLE

Universal MATE-N-LOK Connectors

TE Connectivity (TE)'s LUMAWISE ANSI C136.41 compliant dimming receptacle with Universal MATE-N-LOK connections provide a fully pluggable, electrical and mechanical interconnection between an ANSI C136.41-2013 photo control cell and luminaire. Ideal for outdoor commercial and utility lighting luminaires the LUMAWISE ANSI C136.41 compliant dimming receptacle is available with four dimming contacts to support 0-10 VDC dimming methods and Digitial Addressable Lighting Interface (DALI), while providing a reliable power interconnect with three robust twist lock contacts.



Applications

- Street and Roadway Lighting
- Photo Controls
- Parking Lot Lighting

Electrical

• cUR Recognized to UL 773

• Power Contacts: Current rating: 15 A max

Voltage rating: 480 VAC/DC

• Dimming Contacts: Current rating: 1.5 A max

Voltage rating: 30 VAC/DC

Mechanical

- Conforms to dimensional requirements of ANSI C136.41-2013
- Offers a 7 position version

• **7 position**: 3 power contacts +

4 dimming/signal contacts

- Power contacts terminated to 14AWG stranded wire per UL1015
- Signal contacts terminated to 18AWG stranded wire per UL1015

Specifications

Application Specification: 114-32115
 Product Specification: 108-32059
 Instruction Sheet: 408-32196

Materials

Power Contacts: Copper alloy, tin over nickel plating
 Dimming Contacts: Copper alloy, gold over nickel plating

• Housing: Glass filled PBT, UL 94V-0 flammability rated

Benefits

- Robust twist lock contacts for a reliable power interconnect
- Receptacle comes with wire leads pre-terminated with universal MATE-N-LOK connectors for ease of integration into new or existing light fixtures
- Accepts ANSI standard dimmable photocells to provide a connection between the photocell and the luminaire
- Available with four dimming contacts to support one or two channel dimming protocols




Product Selection Information

	Part Number	Description
	<u>2213785-1</u>	Receptacle Assembly, Dimmable Photocontrol 105C,3/4, Connector
0	2213469-1	Gasket, Photocell Receptacle (sold separately)
	<u>172167-1</u>	4P universal MATE-N-LOK Plug
600	<u>350766-1</u>	3P universal MATE-N-LOK Plug Housing

Dimming receptacles are pre-terminated with Universal MATE-N-LOK connector pns 172167-1 and 350766-1

Dimensions



Dimensions are shown in mm for reference purposes only.

Part Number 2213785-1 Ø 4 . 29 49.2

te.com

© 2017 TE Connectivity. All Rights Reserved. LUMAWISE, MATE-N-LOK, TE, TE Connectivity, and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other logos, product and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

1-1773923-5 BH 06/2017

USA: +1 (800) 522-6752 Canada: +1 (905) 475-6222 Mexico: +52 (0) 55-1106-0800 Latin/S. America: +54 (0) 11-4733-2200 Germany: +49 (0) 6251-133-1999 UK: +44 (0) 800-267666 France: +33 (0) 1-3420-8686 The Netherlands: +31 (0) 73-6246-999 China: +86 (0) 400-820-6015

