TE P/N	TE CD	Nanonics P/N	Part Description
1589467-1	1589467	SSM037L84KN	Dualobe, 1 row, metal, 37 position, rectacle, w/integrated standoffs, vertical mount, surface termination, 1 side exit, .040 extended leads, tin/lead leadframe, 1.0 x .200 mounting screw w/ 4 standoffs, thread for 1.0 jackscrews.
1589467-2	1589467	SSM015L82HN	Dualobe, 1 row, metal, 15 position, receptacle w/ integrated standoffs, vertical mount, surface termination, 1 side exit, .020 extended leads, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589467-3	1589467	SSM005L82HN	Dualobe, 1 row, metal, 5 position, receptacle w/integrated standoffs, vertical mount, surface termination, 1 side exit, .020 extended leads, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589467-4	1589467	SSM005L84HN	Dualobe, 1 row, metal, 5 position, receptacle w/integrated standoffs, vertical mount, surface termination, 1 side exit, .040 extended leads, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589467-5	1589467	SSM015L84HN	Dualobe, 1 row, metal, 15 position, receptacle w/ integrated standoffs, vertical mount, surface termination, 1 side exit, .040 extended leads, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589467-6	1589467	SSM037L82AQ	Dualobe, 1 row, metal, 37 position, receptacle w/integrated standoffs, vertical mount, surface termination, 1 side exit, .020 extended leads, tin/lead leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
1589467-7	1589467	SSM009L82HN	Dualobe, 1 row, metal, 9 position, receptacle w/ integrated standoffs, vertical mount, surface termination, 1 side exit, .020 extended leads, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1589467-8	1589467	SSM005L82AQ	Dualobe, 1 row, metal, 5 position, receptacle w/integrated standoffs, vertical mount, surface termination, 1 side exit, .020 extended leads, tin/lead leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
1589467-9	1589467	SSM009L8AQ	Dualobe, 1 row, metal, 9 position, receptacle w/ integrated standoffs, vertical mount, surface termination, 1 side exit, .020 foot, tin/lead leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
1-1589467-0	1589467	SSM005L84AQ	Dualobe, 1 row, metal, 5 position, receptacle w/integrated standoffs, vertical mount, surface termination, 1 side exit, .040 extended leads, tin/lead leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
1-1589467-1	1589467	SSM051L84HN	Dualobe, 1 row, metal, 51 position, receptacle w/integrated standoffs, vertical mount, surface termination, 1 side exit, .040 extended leads, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.