

TE P/N	TE CD	Nanonics P/N	Part Description
1589469-1	1589469	SSG005M6	Dualobe, 1 row, gold, 5 position, receptacle, horizntal mount, 90 thru hole termination, .090 long, tin/lead leadframe.
1589469-2	1589469	SSG009M6	Dualobe, 1 row, gold, 9 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe.
1589469-3	1589469	SSG015M6	Dualobe, 1 row, gold, 15 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe.
1589469-4	1589469	SSG037M6SN	Dualobe, 1 row, gold, 37 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1589469-6	1589469	SSL005M6SN	Dualobe, 1 row, LCP, 5 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw w/2 standoffs, thread for 1.0 jackscrews.
1589469-7	1589469	SSL009M6D	Dualobe, 1 row, LCP, 9 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.2 x .160 mounting screw w/ 2 standoffs.
1589469-8	1589469	SSL009M6H	Dualobe, 1 row, LCP, 9 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw.
1589469-9	1589469	SSL009M6SN	Dualobe, 1 row, LCP, 9 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1-1589469-0	1589469	SSL015M6D	Dualobe, 1 row, LCP, 15 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.2 x .160 mounting screw w/ 2 standoffs.
1-1589469-1	1589469	SSL015M6N	Dualobe, 1 row, LCP, 15 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, thread for 1.0 jackscrews.
1-1589469-2	1589469	SSL025M6D	Dualobe, 1 row, LCP, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.2 x .160 mounting screw w/ 2 standoffs.
1-1589469-3	1589469	SSL025M6DQ	Dualobe, 1 row, LCP, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.2 x .160 mounting screw w/ 2 standoffs, thread for 1.2 jackscrews.
1-1589469-4	1589469	SSL025M6H	Dualobe, 1 row, LCP, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw.
1-1589469-5	1589469	SSL025M6HN	Dualobe, 1 row, LCP, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
1-1589469-6	1589469	SSL025M6SQ	Dualobe, 1 row, LCP, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw w/ 2 standoffs, thread for 1.2 jackscrews.
1-1589469-7	1589469	SSM005M6SN	Dualobe, 1 row, metal, 5 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
1-1589469-8	1589469	SSM009M6AQ	Dualobe, 1 row, metal, 9 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
1-1589469-9	1589469	SSM009M6CN	Dualobe, 1 row, metal, 9 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
2-1589469-0	1589469	SSM009M6DQ	Dualobe, 1 row, metal, 9 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.2 x .160 mounting screw w/ 2 standoffs, thread for 1.2 jackscrews.
2-1589469-1	1589469	SSM009M6HM	OBSOLETE
2-1589469-2	1589469	SSM009M6HN	Dualobe, 1 row, metal, 9 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
2-1589469-3	1589469	SSM009M6SM	OBSOLETE
2-1589469-4	1589469	SSM009M6SN	Dualobe, 1 row, metal, 9 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw w/2 standoffs, thread for 1.0 jackscrews.
2-1589469-5	1589469	SSM015M6HN	Dualobe, 1 row, metal, 15 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
2-1589469-6	1589469	SSM015M6SN	Dualobe, 1 row, metal, 15 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
2-1589469-7	1589469	SSM025M6DQ	Dualobe, 1 row, metal, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.2 x .160 mounting screw w/ 2 standoffs, thread for 1.2 jackscrews.
2-1589469-8	1589469	SSM025M6HN	Dualobe, 1 row, metal, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screws, thread for 1.0 jackscrews.
3-1589469-0	1589469	SSM025M6SN	Dualobe, 1 row, metal, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
3-1589469-1	1589469	SSM037M6HM	OBSOLETE
3-1589469-2	1589469	SSM037M6HN	Dualobe, 1 row, metal, 37 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
3-1589469-3	1589469	SSM037M6SN	Dualobe, 1 row, metal, 37 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
3-1589469-4	1589469	SSM051M6SN	Dualobe, 1 row, metal, 51 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
3-1589469-5	1589469	SSL009M6A	Dualobe, 1 row, LCP, 9 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.2 x .160 mounting screws.
3-1589469-6	1589469	SSL015M6A	Dualobe, 1 row, LCP, 15 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.2 x .160 mounting screws.
3-1589469-7	1589469	SSL025M6A	Dualobe, 1 row, LCP, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.2 x .160 mounting screws.
3-1589469-8	1589469	SSL015M6CN	Dualobe, 1 row, LCP, 15 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .200 mounting screws w/ 2 standoffs, thread for 1.0 jackscrews.
3-1589469-9	1589469	SSL009M6CN	Dualobe, 1 row, LCP, 9 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
4-1589469-0	1589469	SSL025M6CN	Dualobe, 1 row, LCP, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long tin/lead leadframe, 1.0 x .200 mounting screw w/2 standoffs, thread for 1.0 jackscrews.
4-1589469-1	1589469	SSL037M6SN	Dualobe, 1 row, LCP, 37 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
4-1589469-2	1589469	SSM037M6HQ	Dualobe, 1 row, metal, 37 position, receptacle, horizontal mount, 90 thru hole termination,
4-1589469-3	1589469	SSG051M6HN	Dualobe, 1 row, gold, 51 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
4-1589469-4	1589469	SSM051M6N	Dualobe, 1 row, metal, 51 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, thread for 1.0 jackscrews.
4-1589469-5	1589469	SSL015M6SN	Dualobe, 1 row, LCP, 15 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screws w/ 2 standoffs, thread for 1.0 jackscrews.
4-1589469-6	1589469	SSM025M6AQ	Dualobe, 1 row, metal, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
4-1589469-7	1589469	SSM015M6AQ	Dualobe, 1 row, netal, 15 position, receptacle, horizontal mount, 90 thru hole termination,
4-1589469-8	1589469	SSL005M6CN	Dualobe, 1 row, LCP, 5 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .200 mounting screw w/2 standoffs, thread for 1.0 jackscrews.
4-1589469-9	1589469	SSG009M6SN	Dualobe, 1 row, gold, 9 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
5-1589469-0	1589469	SSL037M6HN	Dualobe, 1 row, LCP, 37 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
5-1589469-1	1589469	SSM051M6HN	Dualobe, 1 row, metal, 51 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
5-1589469-2	1589469	SSL009M6N	Dualobe, 1 row, LCP, 9 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, thread for 1.0 jackscrews.
5-1589469-3	1589469	SSM005M6HN	Dualobe, 1 row, metal, 5 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
5-1589469-4	1589469	SSL015M6AN	Dualobe, 1 row, LCP, 15 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.2 x .160 mounting screws, thread for 1.0 jackscrews.
5-1589469-5	1589469	SSL025M6AN	Dualobe, 1 row, LCP, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.2 x .160 mounting screws, thread for 1.0 jackscrews.