

Nanonics Standard Catalog Part Number Cross-Reference

TE P/N	TE CD	Nanonics P/N	Part Description
1589482-1	1589482	STL025C5N	Dualobe, 2 row, LCP, 25 position, plug, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.0 captive jackscrews.
1589482-2	1589482	STM025C5N	Dualobe, 2 row, metal, 25 position, plug, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.0 captive jackscrews.
1589482-3	1589482	STM051C5N	Dualobe, 2 row, metal, 51 position, plug, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.0 captive jackscrews.
1589482-4	1589482	STM051C5Q	Dualobe, 2 row, metal, 51 position, plug, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.2 captive jackscrews.
1589482-5	1589482	STM065C5Q	Dualobe, 2 row, metal, 65 position, plug, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.2 captive jackscrews.
1589482-6	1589482	STL015C5N	Dualobe, 2 row, LCP, 15 position, plug, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.0 captive jackscrews.
1589482-7	1589482	STM015C5N	Dualobe, 2 row, metal, 15 position, plug, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.0 captive jackscrews.
1589482-8	1589482	STM065C5M	Dualobe, 2 row, metal, 65 position, plug, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.0 non-captive jackscrews.
1589482-9	1589482	STM037C5	Dualobe, 2 row, metal, 37 position, plug, vertical mount, thru hole termination, .090 long, tin/lead leadframe.
1-1589482-0	1589482	STM051C5	Dualobe, 2 row, metal, 51 position, plug, vertical mount, thru hole termination, .090 long, tin/lead leadframe.
1-1589482-1	1589482	STM025C5Q	Dualobe, 2 row, metal, 25 position, plug, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.2 captive jackscrews.
1-1589482-2	1589482	STM037C5Q	Dualobe, 2 row, metal, 37 position, plug, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.2 captive jackscrews.
1-1589482-3	1589482	STM009C5N	Dualobe, 2 row, metal, 9 position, plug, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.0 captive jackscrews.
1-1589482-4	1589482	STM065C5N	Dualobe, 2 row, metal, 65 position, plug, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.0 captive jackscrews.
1-1589482-5	1589482	STM009C5Q	Dualobe, 2 row, metal, 9 position, plug, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.2 captive jackscrews.
1-1589482-6		STM037C5N	Dualobe, 2 row, metal, 37 position, plug, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.0 captive jackscrews.
1-1589482-7	1589482	STM015C5Q	Dualobe, 2 row, metal, 15 position, plug, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.2 captive jackscrews.
1-1589482-8	1589482	STM025C5	Dualobe, 2 row, metal, 25 position, plug, vertical mount, thru hole termination, .090 long, tin/lead leadframe.
1-1589482-9	1589482	STM015C5CN	Dualobe, 2 row, metal, 15 position, plug, vertical mount, thru hole termination, .090 long, tin/lead leadframe, 1.0 x .200 mounting screw w/ two standoffs, 1.0 captive jackscrews.