

7-1589487-3	1589487	STM065M6AQ	Dualobe, 2 row, metal, 65 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
7-1589487-4	1589487	STG065M6SN	Dualobe, 2 row, gold, 65 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
7-1589487-5	1589487	STL015M6KN	Dualobe, 2 row, LCP, 15 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .200 mounting screw w/ 4 standoffs, thread for 1.0 jackscrews.
7-1589487-6	1589487	STL025M6KN	Dualobe, 2 row, LCP, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .200 mounting screw w/ 4 standoffs, thread for 1.0 jackscrews.
7-1589487-7	1589487	STG051M6HN	Dualobe, 2 row, gold, 51 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
7-1589487-8	1589487	STL009M6HN	Dualobe, 2 row, LCP, 9 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
7-1589487-9	1589487	STM037M6CN	Dualobe, 2 row, metal, 37 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
8-1589487-0	1589487	STL051M6AN	Dualobe, 2 row, LCP, 51 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.2 x .160 mounting screw, thread for 1.0 jackscrews.
8-1589487-1	1589487	STL051M6IN	Dualobe, 2 row, LCP, 51 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.2 x .200 mounting screw, thread for 1.0 jackscrews.
8-1589487-2	1589487	STL065M6HN	Dualobe, 2 row, LCP, 65 position, receptacle, horizontal mount, 90 thru termination, .090 long, tin/lead leadframe, 1.0 x .160 mounting screw, thread for 1.0 jackscrews.
8-1589487-3	1589487	STM025M6AQ	Dualobe, 2 row, metal, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
8-1589487-4	1589487	STM015M6AQ	Dualobe, 2 row, metal, 15 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.2 x .160 mounting screw, thread for 1.2 jackscrews.
8-1589487-5	1589487	STL037M6IN	Dualobe, 2 row, LCP, 37 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.2 x .200 mounting screw, thread for 1.0 jackscrews.
8-1589487-6	1589487	STM037M6PQ	Dualobe, 2 row, metal, 37 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.2 x .200 mounting screw w/ 4 standoffs, thread for 1.2 jackscrews.
8-1589487-7	1589487	STG025M6CN	Dualobe, 2 row, gold, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews.
8-1589487-8	1589487	STM065M6AN	Dualobe, 2 row, metal, 65 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.2 x .160 mounting screw, thread for 1.0 jackscrews.
8-1589487-9	1589487	STM009M6N	Dualobe, 2 row, metal, 9 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, thread for 1.0 jackscrews.
9-1589487-0	1589487	STM025M6CN	Dualobe, 2 row, stainless, 25 position, receptacle, horizontal mount, 90 thru hole termination, .090 long, tin/lead leadframe, 1.0 x .200 mounting screw w/ 2 standoffs, thread for 1.0 jackscrews