



### Nanonics Standard Catalog Part Number Cross-Reference

Revision 1

TE P/N	TE CD	Nanonics P/N	Part Description
7-1589671-1	1589735	JSL009PP2DX003N	Jumper, 1 row, LCP, 9 position, plug to plug, 1 to 1, 30 AWG 7 strand, white PTFE wire, 3 inches, 1.0 captive jackscrews.
7-1589671-4	1589735	JSL015PP2DX006N	Jumper, 1 row, LCP, 15 position, plug to plug, 1 to 1, 30 AWG 7 strand, white PTFE wire, 6 inches, 1.0 captive jackscrews.
8-1589671-3	1589735	JSL051PP2DC004N	Jumper, 1 row, LCP, 51 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 4 inches, 1.0 captive jackscrews.
9-1589671-0	1589735	JSM005PP2DC002N	Jumper, 1 row, metal, 5 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 2 inches, 1.0 captive jackscrews.
9-1589671-1	1589735	JSM005PP2DT150N	Jumper, 1 row, metal, 5 position, plug to plug, 1 to 1, 30 AWG 7 strand, white ETFE M22759/33 wire, 150 inches, 1.0 captive jackscrews.
9-1589671-5	1589735	JSM009PP2DC002N	Jumper, 1 row, metal, 9 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 2 inches, 1.0 captive jackscrews.
9-1589671-6	1589735	JSM009PP2DC003N	Jumper, 1 row, metal, 9 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 3 inches, 1.0 captive jackscrews.
9-1589671-7	1589735	JSM009PP2DC024N	Jumper, 1 row, metal, 9 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 24 inches, 1.0 captive jackscrews.
2-1589672-0	1589735	JSM025PP2DX004N	Jumper, 1 row, metal, 25 position, plug to plug, 1 to 1, 30 AWG 7 strand, white PTFE wire, 4 inches, 1.0 captive jackscrews.
2-1589672-1	1589735	JSM025PP2DX008N	Jumper, 1 row, metal, 25 position, plug to plug, 1 to 1, 30 AWG 7 strand, white PTFE wire, 8 inches, 1.0 captive jackscrews.
2-1589672-2	1589735	JSM025PP2DX17N	Jumper, 1 row, metal, 25 position, plug to plug, 1 to 1, 30 AWG 7 strand, white PTFE wire, 17 centimeters, 1.0 captive jackscrews.
2-1589672-5	1589735	JSM025PP4DXC20N	Jumper, 1 row, metal, 25 position, plug to plug, 1 to 1, 34 AWG 7 strand, white PTFE wire, 20 centimeters, 1.0 captive jackscrews.
3-1589672-4	1589735	JSM037PP2DC006Q	Jumper, 1 row, metal, 37 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 6 centimeters, 1.2 captive jackscrews.
3-1589672-5	1589735	JSM037PP2DC008Q	Jumper, 1 row, metal, 37 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 8 centimeters, 1.2 captive jackscrews.
3-1589672-6	1589735	JSM037PP2DX018N	Jumper, 1 row, metal, 37 position, plug to plug, 1 to 1, 30 AWG 7 strand, white PTFE wire, 18 inches, 1.0 captive jackscrews.
5-1589672-3	1589735	JSM051PP2DCC12Q	Jumper, 1 row, metal, 51 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 12 centimeters, 1.2 captive jackscrews.
1589735-1	1589735	JSL025PP2DC012N	Jumper, 1 row, LCP, 25 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 12 inches, 1.0 captive jackscrews.
1589735-2	1589735	JSL015PP2DX001N	Jumper, 1 row, LCP, 15 position, plug to plug, 1 to 1, 30 AWG 7 strand, white PTFE wire, 1 inch, 1.0 captive jackscrews.
1589735-3	1589735	JSM005PP2DC008	Jumper, 1 row, metal, 5 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 8 inches.
1589735-4	1589735	JSM005PP2DC072	Jumper, 1 row, metal, 5 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 72 inches.
1589735-5	1589735	JSM005PP2DC02.5N	Jumper, 1 row, metal, 5 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 2.5 inches, 1.0 captive jackscrews.
1589735-6	1589735	JSM009PP2DM005Q	Jumper, 1 row, metal, 9 position, plug to plug, 1 to 1, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 5 inches, 1.2 captive jackscrews.
1589735-7	1589735	JSL009PP2DX006N	Jumper, 1 row, LCP, 9 position, plug to plug, 1 to 1, 30 AWG 7 strand, white PTFE wire, 6 inches, 1.0 captive jackscrews.
1589735-8	1589735	JSL009PP2DC006N	Jumper, 1 row, LCP, 9 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 6 inches, 1.0 captive jackscrews.
1589735-9	1589735	JSM005PP2DC005N	Jumper, 1 row, metal, 5 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 5 inches, 1.0 captive jackscrews.
1-1589735-0	1589735	JSM005PP2DC003N	Jumper, 1 row, metal, 5 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 3 inches, 1.0 captive jackscrews.
1-1589735-1	1589735	JSM015PP2DC004N	Jumper, 1 row, metal, 15 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 4 inches, 1.0 captive jackscrews.
1-1589735-2	1589735	JSM009PP2DC006N	Jumper, 1 row, metal, 9 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 6 inches, 1.0 captive jackscrews.
1-1589735-3	1589735	JSM015PP2DC006N	Jumper, 1 row, metal, 15 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 6 inches, 1.0 captive jackscrews.
1-1589735-4	1589735	JSM025PP2DC006N	Jumper, 1 row, metal, 25 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 6 inches, 1.0 captive jackscrews.
1-1589735-5	1589735	JSL005PP2DC002N	Jumper, 1 row, LCP, 5 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 2 inches, 1.0 captive jackscrews.
1-1589735-6	1589735	JSM005PP2DC05.5N	Jumper, 1 row, metal, 5 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 5.5 inches, 1.0 captive jackscrews.
1-1589735-7	1589735	JSM005PP2DC001N	Jumper, 1 row, metal, 5 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 1 inches, 1.0 captive jackscrews.
1-1589735-8	1589735	JSM009PP2DC001N	Jumper, 1 row, metal, 9 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 1 inches, 1.0 captive jackscrews.
1-1589735-9	1589735	JSM005PP2DC024Q	Jumper, 1 row, metal, 5 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 24 inches, 1.2 captive jackscrews.
2-1589735-0	1589735	JSM009PP2DC024Q	Jumper, 1 row, metal, 9 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 24 inches, 1.2 captive jackscrews.
2-1589735-1	1589735	JSM015PP2DC024Q	Jumper, 1 row, metal, 15 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 24 inches, 1.2 captive jackscrews.
2-1589735-2	1589735	JSL051PP2DM012N	Jumper, 1 row, LCP, 51 position, plug to plug, 1 to 1, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 12 inches, 1.0 captive jackscrews.
2-1589735-4	1589735	JSM025PP2DC002N	Jumper, 1 row, metal, 25 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 2 inches, 1.0 captive jackscrews.
2-1589735-5	1589735	JSM015PP2DCC04N	Jumper, 1 row, metal, 15 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 4 centimeters, 1.0 captive jackscrews.
2-1589735-6	1589735	JSM009PP2DCC03N	Jumper, 1 row, metal, 9 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 3 centimeters, 1.0 captive jackscrews.