



Nanonics Standard Catalog Part Number Cross-Reference

Revision 1

TE P/N	TE CD	Nanonics P/N	Part Description
1589811-1	1589811	USS037H2	Unshrouded, 1 row, strip, 37 position, plug, horizontal mount, surface termination, .020 foot, gold leadframe.
1589811-2	1589811	USS004H2T	Unshrouded, 1 row, strip, 4 position, plug, horizontal mount, surface termination, .020 foot, gold leadframe, guide post in position 1
1589811-3	1589811	USS004H2	Unshrouded, 1 row, strip, 4 position, plug, horizontal mount, surface termination, .020 foot, gold leadframe.
1589811-4	1589811	USS009H2	Unshrouded, 1 row, strip, 9 position, plug, horizontal mount, surface termination, .020 foot, gold leadframe.
1589811-5	1589811	USS009H2T	Unshrouded, 1 row, strip, 9 position, plug, horizontal mount, surface termination, .020 foot, gold leadframe, guide post in position 1
1589811-6	1589811	USS015H2	Unshrouded, 1 row, strip, 15 position, plug, horizontal mount, surface termination, .020 foot, gold leadframe.