

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories  
→ Female Plugs

## General Information

<b>Extended Product Type:</b>	CPFT2/4
<b>Product ID:</b>	1SNA094304R2300
<b>EAN:</b>	3472590943048
<b>Catalog Description:</b>	CPFT2/4 Female Plugs Black

## Ordering

<b>Color:</b>	Black
<b>Minimum Order Quantity:</b>	60 piece
<b>Customs Tariff Number:</b>	85369010

## Dimensions

<b>Product Net Width:</b>	20.2 mm
<b>Product Net Height:</b>	20.8 mm
<b>Product Net Depth / Length:</b>	15 mm
<b>Product Net Weight:</b>	6.4 g

## Technical

<b>Rated Cross-Section:</b>	2.5 mm <sup>2</sup>
<b>Spacing:</b>	5.08 mm
<b>Connection Type:</b>	Screw clamp
<b>Function:</b>	Female Plugs
<b>Connecting Capacity Main Circuit:</b>	Screw Clamp / Flexible 1x 0.22 ... 2.5 mm <sup>2</sup> Screw Clamp / Rigid 1x 0.2 ... 4 mm <sup>2</sup>
<b>Rated Current (I<sub>n</sub>):</b>	Main Circuit 12 A
<b>Rated Short-time Withstand Current (I<sub>cw</sub>):</b>	for 1 s 300 A
<b>Rated Voltage (U<sub>r</sub>):</b>	250 V
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Insulation Material:</b>	Polyamide
<b>Wire Stripping Length:</b>	7.5 mm
<b>Recommended Screw Driver:</b>	3.5 mm
<b>Tightening Torque:</b>	acc. IEC 60947-1 0.5 N·m Manufacturer 0.8 N·m

<b>Suitable For:</b>	MA2.5/5-2CPE
	MA2.5/5-CPE
	MA2.5/5D-2CPE
	MA2.5/5-SFA-CPE
	MA2.5/5-SNB-CPE

## Technical UL/CSA

<b>Maximum Operating Voltage UL/CSA:</b>	Main Circuit 300 V
--	--------------------

<b>Connecting Capacity UL/CSA:</b>	Stranded 12 AWG
------------------------------------	-----------------

## Certificates and Declarations (Document Number)

<b>CSA Certificate:</b>	1SND164011A0200
-------------------------	-----------------

<b>cUL Certificate:</b>	1SND164000A0202
-------------------------	-----------------

<b>Declaration of Conformity - CE:</b>	1SSD235011C1002
--	-----------------

## Classifications

<b>Object Classification Code:</b>	X
------------------------------------	---

<b>ETIM 4:</b>	EC002638 - Cable connector
----------------	----------------------------

<b>ETIM 5:</b>	EC002638 - Cable connector
----------------	----------------------------

<b>ETIM 6:</b>	EC002638 - Cable connector
----------------	----------------------------

## Container Information

<b>Package Level 1 Units:</b>	60 piece
-------------------------------	----------

<b>Package Level 1 Width:</b>	61 mm
-------------------------------	-------

<b>Package Level 1 Depth / Length:</b>	220 mm
--	--------

<b>Package Level 1 Height:</b>	47 mm
--------------------------------	-------

<b>Package Level 1 Gross Weight:</b>	0.384 kg
--------------------------------------	----------

<b>Package Level 1 EAN:</b>	3472590943048
-----------------------------	---------------

<b>Package Level 2 Units:</b>	1500 piece
-------------------------------	------------

<b>Package Level 3 Units:</b>	28800 piece
-------------------------------	-------------

<b>Product Packing Type:</b>	Box
------------------------------	-----



