

# M10/10.RS.EX



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → Solution Series

## General Information

<b>Extended Product Type:</b>	M10/10.RS.EX
<b>Product ID:</b>	1SNA146212R2600
<b>EAN:</b>	3472591462128
<b>Catalog Description:</b>	M 10/10.RS.Ex Screw Clamp Terminal Blocks
<b>Long Description:</b>	M10/10.RS.Ex Screw Clamp Terminal Blocks Safety.

## Ordering

<b>Color:</b>	grey
<b>Minimum Order Quantity:</b>	25 piece
<b>Customs Tariff Number:</b>	85369010

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNC160004C0204
<b>Instructions and Manuals:</b>	1SNC160004C0204

## Dimensions

<b>Product Net Width:</b>	10 mm
<b>Product Net Height:</b>	54 mm
<b>Product Net Depth / Length:</b>	51.5 mm
<b>Product Net Weight:</b>	30 g

## Technical

<b>Rated Cross-Section:</b>	10 mm <sup>2</sup>
<b>Spacing:</b>	10 mm
<b>Connection Type:</b>	Safety screw clamp
<b>Function:</b>	Safety
<b>Number of Levels:</b>	1
<b>Insulation Material:</b>	Polyamide
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

## Technical UL/CSA

<b>Flammability According to UL94:</b>	V0
--	----

## Environmental

<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment

## Certificates and Declarations (Document Number)

<b>Declaration of Conformity - CE:</b>	1SND225054U1001
<b>EAC Certificate:</b>	1SND161010A1100
<b>Environmental Information:</b>	1SND220023E1002
<b>Instructions and Manuals:</b>	1SNC160004C0204
<b>RoHS Information:</b>	1SND230023F0208

## Classifications

<b>Object Classification Code:</b>	X
<b>ETIM 4:</b>	EC000897 - Feed-through terminal block
<b>ETIM 5:</b>	EC000897 - Feed-through terminal block
<b>ETIM 6:</b>	EC000897 - Feed-through terminal block

## Container Information

<b>Package Level 1 Units:</b>	25 piece
<b>Package Level 1 Width:</b>	62 mm
<b>Package Level 1 Depth / Length:</b>	280 mm
<b>Package Level 1 Height:</b>	64 mm
<b>Package Level 1 Gross Weight:</b>	0.75 kg
<b>Package Level 1 EAN:</b>	3472591462128
<b>Package Level 2 Units:</b>	350 piece
<b>Package Level 2 Gross Weight:</b>	10.5 kg
<b>Package Level 3 Units:</b>	16800 piece
<b>Product Packing Type:</b>	Box

