

Products → Low Voltage Products and Systems → Connection Devices → Test Blocks → Polarity Plugs

General Information

Extended Product Type:	FIP-2/4-2
Product ID:	1SNA166939R2300
EAN:	3472591669398
Catalog Description:	FIP-2/4-2 Polarity Plugs
Long Description:	During normal operation, lids and covers ensure protection of the test sockets from dust and unauthorized use. According to the mounting choice, two options available: — a lid for all types of mounting — a cover required for base mounting ("S/DS" mounting coding) In the case of opened contacts sockets, electrical continuity covers or lids are required. The electrical continuity is provided thanks to inner pins and linking bar.

Ordering

Color:	Blue
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC169001C0211
Instructions and Manuals:	1SNC169008D0201

Dimensions

Product Net Width:	44 mm
Product Net Height:	63 mm
Product Net Depth / Length:	122 mm
Product Net Weight:	105 g

Technical

Function:	Voltage transformers application
Rated Voltage (U_r):	400 V

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225003U1001
EAC Certificate:	1SND160001A1100
Environmental Information:	1SND220073E1000
Instructions and Manuals:	1SNC169008D0201

Classifications

Object Classification Code:	X
ETIM 4:	EC000902 - (Knife) disconnect terminal block
ETIM 5:	EC000902 - (Knife) disconnect terminal block
ETIM 6:	EC000902 - (Knife) disconnect terminal block

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	77 mm
Package Level 1 Depth / Length:	120 mm
Package Level 1 Height:	48 mm
Package Level 1 Gross Weight:	0.105 kg
Package Level 1 EAN:	3472591669398
Package Level 2 Units:	25 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	500 mm
Package Level 2 Height:	150 mm
Package Level 3 Units:	1200 piece
Product Packing Type:	Box

