

Products → Low Voltage Products and Systems → Connection Devices → Test Blocks → Current Sockets

General Information

Extended Product Type:	CC-E-VA-R2-6.6
Product ID:	1SNA166976R0000
EAN:	3472591669763
Catalog Description:	CC-E-VA-R2-6.6 Current Sockets
Long Description:	Short-circuited type contacts for measurement, calibration and distribution applications. Make before break principle: — The circuit is automatically shorted with the insertion of the plug. — The circuit closes automatically when the plug is removed. — This system guarantees a complete safety. — By convention, green coding is for current circuit.

Ordering

Color:	Green
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC169001C0211
Instructions and Manuals:	1SNC169001C0211

Dimensions

Product Net Width:	50 mm
Product Net Height:	74 mm
Product Net Depth / Length:	57 mm
Product Net Weight:	170 g

Technical

Connection Type:	Ring - Tongue
Function:	Current transformers application
Connecting Capacity Main Circuit:	Stud / Flexible 1x 0.34 ... 10 mm ²
Rated Current (I_n):	Main Circuit 15 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 200 A
Rated Voltage (U_r):	400 V
Rated Impulse Withstand Voltage (U_{imp}):	4000 V
Pollution Degree:	3

Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polycarbonate

Environmental

Ambient Air Temperature:	Operation -10 ... +55 °C Storage -25 ... +70 °C
---------------------------------	--

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225003U1001
EAC Certificate:	1SND160001A1100
Environmental Information:	1SND220073E1000
Instructions and Manuals:	1SNC169001C0211

Classifications

Object Classification Code:	X
ETIM 4:	EC000902 - (Knife) disconnect terminal block
ETIM 5:	EC000902 - (Knife) disconnect terminal block
ETIM 6:	EC000902 - (Knife) disconnect terminal block

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Gross Weight:	8.5 kg
Package Level 1 EAN:	3472591669763
Package Level 2 Units:	50 piece
Package Level 3 Units:	2400 piece
Product Packing Type:	Box

