

Products → Low Voltage Products and Systems → Connection Devices → Test Blocks → Current Sockets

General Information

Extended Product Type:	CC-E-VA-6.6-AG
Product ID:	1SNA166986R0000
EAN:	3472591669862
Catalog Description:	CC-E-VA-6.6-AG Current Sockets
Long Description:	— Designed for high density wiring inside panels. — Alternative to large terminal strips. — Allows easy circuits disconnection without wiring modification. Multi-circuit blocks can be mounted side by side for compact panel board wiring in replacement of large terminal strip.

Ordering

Color:	Green
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SND250028Z1700
Instructions and Manuals:	1SND250028Z1700

Dimensions

Product Net Width:	50 mm
Product Net Height:	74 mm
Product Net Depth / Length:	57 mm
Product Net Weight:	150 g

Technical

Connection Type:	Ring - Tongue
Connecting Capacity Main Circuit:	Stud / Flexible 1x 0.34 ... 10 mm ²
Rated Current (I_n):	Main Circuit 15 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 200 A
Rated Voltage (U_r):	400 V
Rated Impulse Withstand Voltage (U_{imp}):	4000 V
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polycarbonate

Environmental

Ambient Air Temperature:	Operation -10 ... +55 °C Storage -25 ... +70 °C
---------------------------------	--

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225003U1001
EAC Certificate:	1SND160001A1100
Environmental Information:	1SND220073E1000
Instructions and Manuals:	1SND250028Z1700

Classifications

Object Classification Code:	X
ETIM 4:	EC000902 - (Knife) disconnect terminal block
ETIM 5:	EC000902 - (Knife) disconnect terminal block
ETIM 6:	EC000902 - (Knife) disconnect terminal block

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Gross Weight:	0.009 kg
Package Level 1 EAN:	3472591669862
Package Level 2 Units:	50 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	400 mm
Package Level 2 Height:	200 mm
Package Level 3 Units:	2400 piece
Product Packing Type:	Box

