

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → SNA Series

## General Information

<b>Extended Product Type:</b>	M4/8.SF.V0
<b>Product ID:</b>	1SNA195657R2600
<b>EAN:</b>	3472591956573
<b>Catalog Description:</b>	M4/8.SF.V0 Screw Clamp Terminal Blocks - For 5 x 20 and 5 x 25 fuses - Beige V0
<b>Long Description:</b>	M4/8.SF.V0 Screw Clamp Terminal Blocks Fuse.

## Ordering

<b>Color:</b>	Beige V0
<b>Minimum Order Quantity:</b>	50 piece
<b>Customs Tariff Number:</b>	85369010

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNC160001C0207-CH-A screw clamp
<b>Instructions and Manuals:</b>	1SNC160001C0207-CH-A screw clamp

## Dimensions

<b>Product Net Width:</b>	8 mm
<b>Product Net Height:</b>	56.5 mm
<b>Product Net Depth / Length:</b>	41 mm
<b>Product Net Weight:</b>	14 g

## Technical

<b>Rated Cross-Section:</b>	4 mm <sup>2</sup>
<b>Spacing:</b>	8 mm
<b>Connection Type:</b>	Screw clamp
<b>Function:</b>	Fuse
<b>Number of Levels:</b>	1
<b>Rated Impulse Withstand Voltage (U<sub>imp</sub>):</b>	8 kV
<b>Pollution Degree:</b>	2
<b>Insulation Material:</b>	Polyamide
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Wire Stripping Length:</b>	9.5 mm

<b>Recommended Screw Driver:</b>	4 mm
<b>Tightening Torque:</b>	acc. IEC 60947-1 0.5 N·m Manufacturer 0.8 N·m

## Technical UL/CSA

<b>Flammability According to UL94:</b>	V0
--	----

## Environmental

<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment

## Certificates and Declarations (Document Number)

<b>CSA Certificate:</b>	1SND161066A0201
<b>Declaration of Conformity - CE:</b>	1SND225016U1000
<b>EAC Certificate:</b>	1SND161009A1100
<b>Environmental Information:</b>	1SND220021E1002
<b>Instructions and Manuals:</b>	1SNC160001C0207-CH-A screw clamp
<b>RMRS Certificate:</b>	1SND161007A1101
<b>RoHS Information:</b>	1SND230023F0208

## Classifications

<b>Object Classification Code:</b>	X
<b>ETIM 4:</b>	EC000899 - Fuse terminal block
<b>ETIM 5:</b>	EC000899 - Fuse terminal block
<b>ETIM 6:</b>	EC000899 - Fuse terminal block

## Container Information

<b>Package Level 1 Units:</b>	50 piece
<b>Package Level 1 Width:</b>	101 mm
<b>Package Level 1 Depth / Length:</b>	265 mm
<b>Package Level 1 Height:</b>	47 mm
<b>Package Level 1 Gross Weight:</b>	0.7 kg
<b>Package Level 1 EAN:</b>	3472591956573
<b>Package Level 2 Units:</b>	450 piece
<b>Package Level 2 Width:</b>	300 mm
<b>Package Level 2 Depth / Length:</b>	500 mm
<b>Package Level 2 Height:</b>	150 mm
<b>Package Level 2 Gross Weight:</b>	6.2 kg
<b>Package Level 3 Units:</b>	21600 piece

Product Packing Type:

Box

