

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → SNA Series

## General Information

<b>Extended Product Type:</b>	D4/6.P.T1
<b>Product ID:</b>	1SNA199220R0000
<b>EAN:</b>	3472591992205
<b>Catalog Description:</b>	D4/6.P.T1 Screw Clamp Terminal Blocks - Triple deck - Green-Yellow
<b>Long Description:</b>	- Reliable electrical and mechanical contact with the rail, - Ease ground distribution on 7 independent screw clamps.

## Ordering

<b>Color:</b>	Green-Yellow
---------------	--------------

<b>Minimum Order Quantity:</b>	25 piece
--------------------------------	----------

<b>Customs Tariff Number:</b>	85369010
-------------------------------	----------

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNC160019C0202
---	-----------------

<b>Instructions and Manuals:</b>	1SNC160019C0202
----------------------------------	-----------------

## Dimensions

<b>Product Net Width:</b>	6 mm
---------------------------	------

<b>Product Net Height:</b>	90 mm
----------------------------	-------

<b>Product Net Depth / Length:</b>	64.5 mm
------------------------------------	---------

<b>Product Net Weight:</b>	33 g
----------------------------	------

## Technical

<b>Rated Cross-Section:</b>	4 mm <sup>2</sup>
-----------------------------	-------------------

<b>Spacing:</b>	6 mm
-----------------	------

<b>Connection Type:</b>	Screw clamp
-------------------------	-------------

<b>Function:</b>	Ground
------------------	--------

<b>Number of Levels:</b>	4
--------------------------	---

<b>Connecting Capacity Main Circuit:</b>	Screw Clamp / Flexible 1x 0.22 ... 4 mm <sup>2</sup> Screw Clamp / Rigid 1x 0.2 ... 4 mm <sup>2</sup>
--	--

<b>Gauge Type:</b>	A4
--------------------	----

<b>Rated Short-time Withstand Current (I<sub>cw</sub>):</b>	for 1 s 480 A
---	---------------

<b>Pollution Degree:</b>	3
--------------------------	---

<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
------------------------------	--

<b>Insulation Material:</b>	Polyamide
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Wire Stripping Length:</b>	9.5 mm
<b>Recommended Screw Driver:</b>	4 mm
<b>Tightening Torque:</b>	acc. IEC 60947-1 0.5 N·m Manufacturer 0.8 N·m

## Technical UL/CSA

<b>Connecting Capacity Main Circuit UL/CSA:</b>	Screw Clamp / Rigid 1x 22 ... 12 AWG
<b>Connecting Capacity UL/CSA:</b>	Screw Clamp / Rigid 22 ... 12 AWG Stranded 12 AWG
<b>Flammability According to UL94:</b>	V0

## Environmental

<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment

## Certificates and Declarations (Document Number)

<b>Declaration of Conformity - CE:</b>	1SND225017U1000
<b>EAC Certificate:</b>	1SND161009A1100
<b>Environmental Information:</b>	1SND220004E1002
<b>Instructions and Manuals:</b>	1SNC160019C0202
<b>RMRS Certificate:</b>	1SND161007A1101
<b>RoHS Information:</b>	1SND230023F0208

## Classifications

<b>Object Classification Code:</b>	X
<b>ETIM 4:</b>	EC000901 - Ground terminal block
<b>ETIM 5:</b>	EC000901 - Ground terminal block
<b>ETIM 6:</b>	EC000901 - Ground terminal block

## Container Information

<b>Package Level 1 Units:</b>	25 piece
<b>Package Level 1 Width:</b>	147 mm
<b>Package Level 1 Depth / Length:</b>	117 mm
<b>Package Level 1 Height:</b>	97 mm
<b>Package Level 1 Gross Weight:</b>	0.825 kg

<b>Package Level 1 EAN:</b>	3472591992205
-----------------------------	---------------

<b>Package Level 2 Units:</b>	375 piece
-------------------------------	-----------

<b>Package Level 2 Width:</b>	300 mm
-------------------------------	--------

<b>Package Level 2 Depth / Length:</b>	500 mm
--	--------

<b>Package Level 2 Height:</b>	300 mm
--------------------------------	--------

<b>Package Level 2 Gross Weight:</b>	12.950 kg
--------------------------------------	-----------

<b>Product Packing Type:</b>	Box
------------------------------	-----

