

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Circuit Separators

General Information

Extended Product Type:	SCH8
Product ID:	1SNA199412R1500
EAN:	3472591994124
Catalog Description:	SCH8 Circuit Separators Beige
Long Description:	SCH8 - Circuit Separators - Beige - 1.2mm Spacing.

Ordering

Color:	Beige
Minimum Order Quantity:	25 piece
Customs Tariff Number:	39269097

Dimensions

Product Net Width:	1.2 mm
Product Net Height:	54 mm
Product Net Depth / Length:	55 mm
Product Net Weight:	4.8 g

Technical

Spacing:	1.2 mm
Function:	Circuit Separators
Insulation Material:	Polyamide
Mounting on DIN Rail:	Type 2 (21.8 x 8.2 mm Mounting Rail) acc. to NFC 93461 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Suitable For:	H6/24.DH HD120/30.F10 HD185/36.F12 HD6/13.FF4 HD6/14 HD6/22.F12G HD6/30.F12G HD6/9 HD70/22.F8

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C
---------------------------------	---------------------------

Certificates and Declarations (Document Number)

Environmental Information: 1SND220090E1000

Classifications

Object Classification Code: X

ETIM 4: EC000886 - Endplate and partition plate for terminal block

ETIM 5: EC000886 - Endplate and partition plate for terminal block

ETIM 6: EC000886 - Endplate and partition plate for terminal block

Container Information

Package Level 1 Units: 25 piece

Package Level 1 Gross Weight: 0.12 kg

Package Level 1 EAN: 3472591994124



