

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories → Spacers

General Information

Extended Product Type:	INHD1
Product ID:	1SNA295427R1400
EAN:	3472592954271
Catalog Description:	INHD1 Spacers - Beige - 1.2 mm 0.047 in

Ordering

Color:	Beige
Minimum Order Quantity:	25 piece
Customs Tariff Number:	39269097

Dimensions

Product Net Width:	1.2 mm
Product Net Height:	50 mm
Product Net Depth / Length:	18 mm
Product Net Weight:	2 g

Technical

Spacing:	1.2 mm
Function:	Spacers
Insulation Material:	Polyamide
Mounting on DIN Rail:	Type 2 (21.8 x 8.2 mm Mounting Rail) acc. to NFC 93461 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Suitable For:	HD10/12.F5 HD10/12.FF5 HD120/30.F10 HD185/36.F12 HD35/16.F6 HD4/10.F4.19 HD4/9.F4 HD70/22.F8

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C
---------------------------------	---------------------------

Classifications

Object Classification Code:	X
------------------------------------	---

Container Information

Package Level 1 Units: 25 piece

Package Level 1 Gross Weight: 0.05 kg

Package Level 1 EAN: 3472592954271

Package Level 2 Units: 2000 piece