

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → SNA Series

General Information

Extended Product Type:	D4/8.D2.P.SFL
Product ID:	1SNA400271R1500
EAN:	3472594002710
Catalog Description:	D4/8.D2.P.SFL Screw Clamp Terminal Blocks - For 5 x 20 and 5 x 25 fuses - with blown fuse indicator - Grey
Long Description:	- Protect your circuits with 5x20 and 5x25 fuse terminal blocks (fuse not supplied with terminal blocks), - Save space with double deck terminal blocks: 2 independent circuits 1 fuse on upper deck + 1 feed-through + 1 grounded, - Quickly identify the defective circuit thanks to the blown fuse indicator.

Ordering

Color:	Grey
Minimum Order Quantity:	25 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160019C0202
Instructions and Manuals:	1SNC160019C0202

Dimensions

Product Net Width:	8 mm
Product Net Height:	99.1 mm
Product Net Depth / Length:	64.5 mm
Product Net Weight:	35 g

Technical

Rated Cross-Section:	4 mm ²
Spacing:	8 mm
Connection Type:	Screw clamp
Function:	Fuse
Number of Levels:	2
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.5 ... 4 mm ² Screw Clamp / Rigid 1x 0.5 ... 6 mm ²
Gauge Type:	A4
Rated Current (I_n):	Main Circuit 6.3 A
Rated Voltage (U_r):	300 V

Rated Impulse Withstand Voltage (U_{imp}):	6000 V
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	9.5 mm
Recommended Screw Driver:	4 mm
Tightening Torque:	acc. IEC 60947-1 0.5 N·m Manufacturer 0.8 N·m

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 300 V
Connecting Capacity Main Circuit UL/CSA:	Screw Clamp / Rigid 1x 20 ... 12 AWG
Connecting Capacity UL/CSA:	Screw Clamp / Rigid 24 ... 12 AWG Stranded 12 AWG

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
---------------------------------	--

Certificates and Declarations (Document Number)

CSA Certificate:	1SND161081A0200
cUL Certificate:	1SND161049A0200
Declaration of Conformity - CE:	1SND225040U1000
EAC Certificate:	1SND161009A1100
Environmental Information:	1SND220021E1002
Instructions and Manuals:	1SNC160019C0202

Classifications

Object Classification Code:	X
ETIM 4:	EC000899 - Fuse terminal block
ETIM 5:	EC000899 - Fuse terminal block
ETIM 6:	EC000899 - Fuse terminal block

Container Information

Package Level 1 Units:	25 piece
Package Level 1 Width:	135 mm

Package Level 1 Depth / Length:	175 mm
Package Level 1 Height:	74 mm
Package Level 1 Gross Weight:	0.875 kg
Package Level 1 EAN:	3472594002710
Package Level 2 Units:	400 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	500 mm
Package Level 2 Height:	300 mm
Package Level 3 Units:	56000 piece
Product Packing Type:	Box

