

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → SNA Series

## General Information

|                               |  |
|-------------------------------|--|
| <b>Extended Product Type:</b> | D95/26.P   |
| <b>Product ID:</b>            | 1SNA400620R1700  |
| <b>EAN:</b>                   | 3472599997851  |
| <b>Catalog Description:</b>   | D95/26.P Screw Clamp Terminal Blocks - Ground - Green-Yellow |
| <b>Long Description:</b>      | Reliable electrical and mechanical contact with the rail.    |

## Ordering

|                                |              |
|--------------------------------|--------------|
| <b>Color:</b>                  | Green-Yellow |
| <b>Minimum Order Quantity:</b> | 10 piece     |
| <b>Customs Tariff Number:</b>  | 85369010     |

## Popular Downloads

|   |                 |
|---|-----------------|
| <b>Data Sheet, Technical Information:</b> | 1SNC160019C0202 |
| <b>Instructions and Manuals:</b>          | 1SNC160019C0202 |

## Dimensions

|                                    |         |
|------------------------------------|---------|
| <b>Product Net Width:</b>          | 26 mm   |
| <b>Product Net Height:</b>         | 87 mm   |
| <b>Product Net Depth / Length:</b> | 85.2 mm |
| <b>Product Net Weight:</b>         | 278 g   |

## Technical

|   |  |
|---|--|
| <b>Rated Cross-Section:</b>                                 | 95 mm <sup>2</sup>   |
| <b>Spacing:</b>   | 26 mm  |
| <b>Connection Type:</b>                                     | Screw clamp  |
| <b>Function:</b>  | Ground   |
| <b>Number of Levels:</b>                                    | 1  |
| <b>Connecting Capacity Main Circuit:</b>                    | Screw Clamp / Flexible 1x 35 ... 95 mm <sup>2</sup><br>Screw Clamp / Rigid 1x 35 ... 120 mm <sup>2</sup><br>Screw Clamp / With Insulated Ferrule 1x 50 mm <sup>2</sup> |
| <b>Gauge Type:</b>  | B12  |
| <b>Rated Short-time Withstand Current (I<sub>cw</sub>):</b> | for 1 s 11400 A  |
| <b>Rated Impulse Withstand Voltage (U<sub>imp</sub>):</b>   | 8000 V   |
| <b>Dielectric Test Voltage:</b>                             | 3500 V   |

|                                  |  |
|----------------------------------|--|
| <b>Pollution Degree:</b>         | 3  |
| <b>Degree of Protection:</b>     | acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP10 |
| <b>Insulation Material:</b>      | Polyamide  |
| <b>Mounting on DIN Rail:</b>     | TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715         |
| <b>Wire Stripping Length:</b>    | 26.0 mm  |
| <b>Recommended Screw Driver:</b> | 6 mm   |
| <b>Tightening Torque:</b>        | acc. IEC 60947-1 9 N·m<br>Manufacturer 9.5 N·m               |

## Technical UL/CSA

|   |  |
|---|--|
| <b>Connecting Capacity Main Circuit<br/>UL/CSA:</b> | Screw Clamp / Flexible 1x 2 ... 0000 AWG<br>Screw Clamp / Rigid 1x 2 ... 0000 AWG<br>Screw Clamp / With Insulated Ferrule 1x 2 ... 0 AWG |
| <b>Connecting Capacity UL/CSA:</b>                  | Screw Clamp / Rigid 2 ... 0000 AWG<br>Stranded 0 AWG   |
| <b>Flammability According to UL94:</b>              | V0   |

## Environmental

|  |  |
|--|--|
| <b>Ambient Air Temperature:</b>                            | Operation -55 ... +110 °C<br>Storage -55 ... +110 °C |
| <b>Resistance to Vibrations acc. to<br/>IEC 60068-2-6:</b> | Compliant  |

## Certificates and Declarations (Document Number)

|  |                 |
|--|-----------------|
| <b>CSA Certificate:</b>                | 1SND161051A0202 |
| <b>cUL Certificate:</b>                | 1SND161059A0200 |
| <b>Declaration of Conformity - CE:</b> | 1SND225017U1000 |
| <b>EAC Certificate:</b>                | 1SND161009A1100 |
| <b>Environmental Information:</b>      | 1SND220004E1002 |
| <b>Instructions and Manuals:</b>       | 1SNC160019C0202 |
| <b>RMRS Certificate:</b>               | 1SND161007A1101 |

## Classifications

|                                    |                                  |
|------------------------------------|----------------------------------|
| <b>Object Classification Code:</b> | X                                |
| <b>ETIM 4:</b>                     | EC000901 - Ground terminal block |
| <b>ETIM 5:</b>                     | EC000901 - Ground terminal block |
| <b>ETIM 6:</b>                     | EC000901 - Ground terminal block |

## Container Information

|                               |          |
|-------------------------------|----------|
| <b>Package Level 1 Units:</b> | 10 piece |
| <b>Package Level 1 Width:</b> | 135 mm   |

|  |               |
|--|---------------|
| <b>Package Level 1 Depth / Length:</b> | 177 mm        |
| <b>Package Level 1 Height:</b>         | 87 mm         |
| <b>Package Level 1 Gross Weight:</b>   | 2.78 kg       |
| <b>Package Level 1 EAN:</b>            | 3472599997851 |
| <b>Package Level 2 Units:</b>          | 30 piece      |
| <b>Package Level 2 Width:</b>          | 200 mm        |
| <b>Package Level 2 Depth / Length:</b> | 300 mm        |
| <b>Package Level 2 Height:</b>         | 200 mm        |
| <b>Package Level 3 Units:</b>          | 2880 piece    |
| <b>Product Packing Type:</b>           | Box           |

