

# PC-RG6-4



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories  
→ Lateral Jumper Bars

## General Information

<b>Extended Product Type:</b>	PC-RG6-4
<b>Product ID:</b>	1SNA519104R0400
<b>EAN:</b>	3472599857612
<b>Catalog Description:</b>	PC-RG6-4 Lateral Jumper Bar - 4 poles - Orange
<b>Long Description:</b>	- Lateral jumper bar for ring lug terminal block, - Allow the connection of consecutive blocks, - Compatible with RGW terminal block of 11 mm 0.433 in spacing

## Ordering

<b>Color:</b>	Orange
<b>Minimum Order Quantity:</b>	15 piece
<b>Customs Tariff Number:</b>	85369010

## Dimensions

<b>Product Net Width:</b>	3.1 mm
<b>Product Net Height:</b>	38.6 mm
<b>Product Net Length:</b>	26.7 mm
<b>Product Net Depth / Length:</b>	26.3 mm
<b>Product Net Weight:</b>	7.33 g

## Technical

<b>Spacing:</b>	11 mm
<b>Function:</b>	Jumper Bars
<b>Rated Current (<math>I_n</math>):</b>	Main Circuit 41 A
<b>Rated Voltage (<math>U_r</math>):</b>	1000 V
<b>Rated Impulse Withstand Voltage (<math>U_{imp}</math>):</b>	8000 V
<b>Power Loss:</b>	1.3 W
<b>Insulation Material:</b>	Polyamide
<b>Suitable For:</b>	RGW6 RGW6-R1 RGW6-ST-1 RGW6-T

## Technical UL/CSA

<b>Maximum Operating Voltage UL/CSA:</b>	Main Circuit 600 V
<b>Connecting Capacity UL/CSA:</b>	Stranded 10 AWG
<b>Flammability According to UL94:</b>	V0

## Environmental

<b>Ambient Air Temperature:</b>	Operation -40 ... +100 °C Storage -40 ... +100 °C
<b>RoHS Status:</b>	Following EU Directive 2011/65/EU

## Certificates and Declarations (Document Number)

<b>Declaration of Conformity - CE:</b>	1SND225158C1001
<b>Environmental Information:</b>	1SND220070E1001
<b>RoHS Information:</b>	1SND230547F0201

## Classifications

<b>ETIM 4:</b>	EC000489 - Cross-connector for terminal block
<b>ETIM 5:</b>	EC000489 - Cross-connector for terminal block
<b>ETIM 6:</b>	EC000489 - Cross-connector for terminal block

## Container Information

<b>Package Level 1 Units:</b>	15 piece
<b>Package Level 1 Width:</b>	65 mm
<b>Package Level 1 Depth / Length:</b>	55 mm
<b>Package Level 1 Height:</b>	31 mm
<b>Package Level 1 Gross Weight:</b>	0.12 kg
<b>Package Level 1 EAN:</b>	3472599857612
<b>Package Level 2 Units:</b>	2100 piece
<b>Package Level 2 Width:</b>	230 mm
<b>Package Level 2 Depth / Length:</b>	350 mm
<b>Package Level 2 Height:</b>	230 mm
<b>Package Level 3 Units:</b>	67200 piece
<b>Product Packing Type:</b>	Box

